



ACCESSORIES

STRING TRIMMER LINE & ACCESSORIES

Part No.	Description
49-16-2714	Easy Load Trimmer Head
49-16-2722	Shoulder Strap
49-16-2810	.080" x 25' Pre-Cut Twisted Trimmer Line – 5 PK
49-16-2712	.080" x 150' Twisted Trimmer Line
49-16-2811	.080" x 320' (1 lb.) Twisted Trimmer Line
49-16-2812	.080" x 940' (3 lbs.) Twisted Trimmer Line
49-16-2782	.095" x 20' Pre-Cut Twisted Trimmer Line – 5 PK
49-16-2713	.095" x 250' (1 lb.) Twisted Trimmer Line
49-16-2783	.095" x 750' (3 lbs.) Twisted Trimmer Line
49-16-2813	.095" x 1250' (5 lbs.) Twisted Trimmer Line
49-16-2800	.105" x 180' (1 lb.) Twisted Trimmer Line
49-16-2789	.105" x 625' (3 lbs.) Twisted Trimmer Line
49-16-2814	.105" x 920' (5 lbs.) Twisted Trimmer Line
49-16-2784	M18 FUEL™ QUIK-LOK™ Attachment Hanger
49-16-2785	M18 FUEL™ QUIK-LOK™ Attachment Hanger – 3 PK

BLADES

Part No.	Description
42-26-2718	8" Edger Blade
49-16-2815	8" Edger Blade – 5 PK
49-16-2816	8" Edger Blade – 50 PK
49-16-2734	21" Mower Blade
49-16-2735	21" Mulching Mower Blade
49-16-2757	9" 4-Cutter Brush Blade
49-16-2799	9" Reciprocator Blades
49-16-2801	Bed Redefiner Blade

CASES & COVERS

Part No.	Description
49-16-2736	21" Mower Cover
49-16-2746	Top Handle Chainsaw Case
49-16-2747	Chainsaw Case

NAILING

Part No.	Description
MDP8D-2000	8D 2-1/4" x .131" Collated Duplex Nails
MDP16D-2000	16D 3" x .131" Collated Duplex Nails

BLOWER ATTACHMENTS & ACCESSORIES

Part No.	Description
49-16-2790	M18 FUEL™ Blower Gutter Attachment
49-16-2791	M18 FUEL™ Blower Angled Flare Attachment
49-16-2797	M18 FUEL™ Blower Tapered and Flat Nozzle Attachment Kit
49-16-2798	M18 FUEL™ Dual Battery Backpack Blower Hip Belt

SAW CHAINS

Part No.	Description
49-16-2732	6" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2750	8" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2817	8" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain – 3 PK
49-16-2759	10" .325" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2723	10" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2742	12" .325" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2744	14" .325" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2819	14" .325" LOW PROFILE™ Pitch, .043" Gauge Saw Chain – 3 PK
49-16-2749	14" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2715	16" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain
49-16-2752	20" .325" Pitch, .050" Gauge Saw Chain

GUIDE BARS

Part No.	Description
49-16-2733	6" 3/8" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
49-16-2751	8" 3/8" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
49-16-2760	10" .325" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
48-09-5001	10" 3/8" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
49-16-2743	12" .325" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
49-16-2745	14" .325" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
49-16-2756	14" 3/8" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
48-09-3001	16" 3/8" LOW PROFILE™ Pitch, .043" Gauge Guide Bar
49-16-2755	20" .325" Pitch, .050" Gauge Guide Bar

SAW CHAIN & GUIDE BAR SETS

Part No.	Description
49-16-2818	8" 3/8" LOW PROFILE™ Pitch, .043" Gauge Saw Chain and Guide Bar Set
49-16-2820	14" .325" LOW PROFILE™ Pitch, .043" Gauge Saw Chain and Guide Bar Set