




Part No.	Size	T in [mm]	R in [mm]	W in [mm]	A in [mm]	B in [mm]	C in [mm]	D in [mm]
077831	0.5"	0.1 [3]	0.4 [10]	0.8 [20]	1.0 [24]	0.9 [23]	0.1 [3]	0.3 [7]
077832	0.75"	0.1 [3]	0.5 [13]	0.8 [20]	1.0 [25]	1.1 [28]	0.2 [6]	0.3 [7]
077833	1"	0.1 [3]	0.6 [16]	1.0 [26]	1.0 [25]	1.3 [34]	0.2 [5]	0.3 [7]
077834	1.25"	0.1 [3]	0.8 [20]	0.9 [23]	1.1 [29]	1.6 [41]	0.2 [6]	0.3 [7]
077835	1.5"	0.2 [4]	0.9 [24]	0.9 [23]	1.6 [42]	1.9 [48]	0.2 [5]	0.4 [10]
077836	2"	0.2 [4]	1.2 [30]	0.9 [23]	1.9 [49]	2.4 [61]	0.6 [15]	0.4 [10]
077838	3"	0.2 [5]	1.8 [45]	1.5 [39]	2.3 [59]	3.4 [85]	0.9 [22]	0.6 [16]
077840	4"	0.3 [7]	2.2 [56]	1.5 [39]	2.4 [62]	4.6 [117]	1.2 [30]	0.6 [16]

SIZES SHOWN ARE FOR REFERENCE 3D MODEL IS TO BE USED FOR MANUFACTURING / VERIFICATION		ALL CHANGES MUST BE APPROVED AND RECORDED BY ENGINEERING		
UNIT: INCHES UNLESS DUAL DIMENSION: INCH (METRIC)	PROJECTION 	IPEX Technologies Inc.		
THIS DRAWING AND ALL TECHNICAL INFORMATION APPEARING HEREON ARE PROPERTY OF IPEX TECHNOLOGIES INC. AND MUST BE KEPT IN CONFIDENCE BY THE RECIPIENT. THE SAME MAY NOT BE USED OR REPRODUCED EITHER IN WHOLE OR IN PART WITHOUT THE EXPRESS CONSENT OF IPEX TECHNOLOGIES INC.		TITLE 1 HOLE PVC COATED STEEL PIPE STRAP		
PAPER SIZE ANSI B	NAME	DATE	SCALE: 1:1	
PART APPEARANCE:	COLOR: White	DRAWN	Z.Liu	1/17/2018
SURFACE FINISHES: (UNLESS OTHERWISE NOTED)		APP'D		
INSIDE:		DIMENSIONS ARE IN INCHES TOLERANCES (UNLESS OTHERWISE SPECIFIED) FRACTIONAL ± 0.01 DECIMAL ± 0.005 .XX ± 0.005 .XXX ± 0.005 ANGULAR ± 1.0		
OUTSIDE:		ALL DIMENSIONS SHOWN ARE AS SHOWN UNLESS NOTED OTHERWISE		
OTHER:		PRODUCT CODE: PROJECT No.		
FILENAME: ☒	FOLDER: ☒			