



# G Series Long Maintained Contact 2-Position Selector Switch Operator - "Off - On"/Blank Nameplate - 1NO/1NC Contact Rating

By Killark  
Catalog # [GO5-2A3F N34](#)



\*Representative Image

G Series - Aluminum Long Maintained Contact 2-Position Selector Switch Operator - "Off - On"/Blank Nameplate - 1NO/1NC Contact Rating.

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

## General

Action	Rotary
Actuator	2 Position Selector Switch
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GO5-2A3F N34
Color	Black
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	1
Series	GO
UPC	783936997209

## Dimensions

Dimensions	6.5 in x 2.25 in x 1.75 in
Gross Weight with Packaging	0.5
Height	1.75 in
Length	6.5 in
Width	2.25 in

## Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A

INRUSH @ 600 VAC; 0.55A  
INRUSH @ 125 VDC; 0.275A  
INRUSH @ 250 VDC; 6A  
BREAKING @ 120 VAC; 3A  
BREAKING @ 240 VAC; 1.5A  
BREAKING @ 480 VAC; 1.2A  
BREAKING @ 600 VAC; 0.55A  
BREAKING @ 125 VDC; 0.275A  
BREAKING @ 250 VDC; 10A  
CARRYING @ 120 VAC; 10A  
CARRYING @ 240 VAC; 10A  
CARRYING @ 480 VAC; 10A  
CARRYING @ 600 VAC; 2.5A  
CARRYING @ 125 VDC; 2.5A  
CARRYING @ 250 VDC.

## Frequency Rating

50/60 Hz

## Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li> <li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li> <li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
Nema Rating	3, 4, 4X
UL File Number	E12379

## Product Assets

- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - GO5-2A3F N34 Specification Sheet French](#)
- [Specifications - G Series Selector Switches Specification Sheet](#)

