


DESCRIPTION

All in one 0-10 V dimmable 4" LED downlight for retrofit & new construction.
Perfect for hospitality, healthcare, shopping mall & retail,
office, exterior soffit, etc.

FEATURES & BENEFITS

- Universal voltage 120-347 V
- 0-10 V Dimmable 5%-100%
- 5 CCT selectable 2700 - 3000 - 3500 - 4000 - 5000 K
- 5 Wattage Adjustable 6 - 8 - 10 - 12 - 16 W
- Type IC, Wet location & Air-tight
- Regressed optics with low glare
- White Trim with White or Silver Matte (Alzak) reflector in stock

DIMENSIONS	ID 3 3/4"	OD 6"	Depth 4 1/8"	Regressed 1 3/8"
	Cut Out 4" to 5"		Ceiling Space needed 4"	



ORDERING GUIDE

DL254-4-16W-M-A5C5	White Trim White Reflector
DL254-4-16W-M-A5C5-AZ	White Trims Silver Reflector (Alzak)

DL254-4-16W-M-A5C5

4" Round Commercial 5 CCT & 5 Wattage Selectable

Project: _____

Location: _____

Qty: _____


Notes: _____

SPECIFICATION						
Applications	Commercial Recessed Ceiling					
Power Levels (W)	CCT / W	6	8	10	12	16
Light Output (lm)	2700K	570	790	1010	1190	1490
	3000K	580	810	1040	1230	1550
	3500K	600	850	1090	1290	1640
	4000K	620	870	1120	1320	1660
	5000K	640	890	1140	1320	1670
Color Temperature (K)	5CCT user selectable: 2700-3000-3500-4000-5000 K					
Beam Angle	80°					
CRI	80					
Input	120V-347V AC 50/60 Hz					
Dimming	0 - 10V					
Approved Location	Insulated Ceiling & Wet Locations					
Air Tight	Yes					
Ambient Temperature	-4°F (-20°C) to +104°F (+40°C)					
Projected Life	70% Light Output at 50,000 Hours					
Certification	cETLus					
Warranty	5 Year					

Trim Options - Matte White and Alzak in stock, other trims available by custom order



ACCESSORIES



Sold Separately

Please note that junction box is not included

Goof Ring White OD 8 1/2" model # [LBL-4CGR-W](#)

New Construction Mounting Plate for Stud Ceiling
model # [LBL-MP-C4-8-STUD](#)

New Construction Mounting Plate for T-bar Ceiling
model # [LBL-MP-C4-10-TBAR](#)

Emergency Driver 8W 120-347V input
model # [BLD-HM08D-YYY](#)

COMPLIANCE



Type IC & Air-Tight
Wet Location

Lotus LED Lights USA

250 H Street # 301, Blaine WA 98230 tel 360-200-5500
Hainesport NJ, Naples FL, Vancouver WA

www.LotusLEDLights.com

mailing addresses
warehouses

Lotus LED Lights CANADA

1080 Cliveden Ave # 6, Delta BC V3M 6G6 tel 604-538-3090
Delta BC & Mississauga ON