

MT200-4



### 4PC Cushion Grip Screwdriver Set (USA)

★★★★★ 4.2 (9)

Our Milwaukee® 4-Piece Cushion Grip Screwdriver Set (USA) is manufactured to give the professional the best-fitting screwdriver with max grip. Our screwdriver tips are custom machined to deliver a precise fit and reduce stripping during demanding fastening applications. For added confidence, the tips are laser etched to increase the gripping surface. Manufactured with high-strength, boron-infused steel for increased hardness, our screwdrivers stand up to the demands of the site with ultimate durability and life. Providing increased versatility, select screwdrivers include a wrench-ready bolster for added torque and a knurled shank for precision control. Quick identification markings on the handle make it easy to identify screwdriver tip size including Phillips, slotted, and cabinet tips. The 4-Piece Set includes screwdrivers offered in 4-inch and 6-inch shank lengths. Our Milwaukee 4-Piece Cushion Grip Screwdriver Set is made in the USA with cutting-edge manufacturing technology and the highest-quality, USA-sourced materials all backed by a complete Lifetime Guarantee.

## INCLUDES

- (1) #2 Phillips 4" Cushion Grip Screwdriver (USA) (MT202)
- (1) 1/4" Slotted 4" Cushion Grip Screwdriver (USA) (MT206)
- (1) 5/16" Slotted 6" Cushion Grip Screwdriver (USA) (MT207)
- (1) 3/16" Cabinet 6" Cushion Grip Screwdriver (USA) (MT212)

### KEY FEATURES

- ✓ Precise Fit – Reduces Stripping
- ✓ Long Lasting – High Strength, Boron-Infused Steel
- ✓ Visible ID Markings
- ✓ Wrench Ready Bolster (select models)
- ✓ Available Tip Types: Cabinet, Phillips, and Slotted
- ✓ Lifetime Guarantee

### SPECIFICATIONS

- ✓ Anti-Slip Tip – Laser Etched
- ✓ Comfortable, Cushion Grip Handle
- ✓ Precision Control Knurled Shank (select models)
- ✓ Includes: #2 Phillips x 4", 1/4" SL x 4", 3/16" Cabinet x 6", 5/16" SL x 6"
- ✓ Available Shank Lengths: 4-inch and 6-inch
- ✓ Made in USA with USA sourced materials

### REVIEWS

### PRODUCT SPECIFICATIONS

Material Composition	Metal Plastic
Length	5.7 in
Weight	0.707 lb

Height	10.68 in
Width	1.1 in
Set Size	4PC