


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs (g)
	MIN. in (mm)	MAX. in (mm)									
PLT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PLT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PLT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PLT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2223)
PLT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PLT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

							TITLE																			
							PREMIUM NON-RELEASABLE - LASHING TIES																			
							CUSTOMER DRAWING																			
							ITEM REVISION NAME					W10001EG/02														
							DATASET FILE NAME					W10001EG_DC/02														
11A	9.12.24	BWG	JADE	DJSL	UPDATED TITLE BLOCK WITH ALTERNATE DESCRIPTION					005806/00					MATERIAL: NYLON 6/6											
10	4/21/21	BWG	MPH	JADE	REVISED "E" DIMENSION.					099443/00																
9	8/13/13	BWG	KJM	RTFI	UPDATED TITLE BORDER AND NOTE 1. SEE ECN FOR DETAILS.					SS-6512/09					DRAWING NUMBER: SS-6512											
REV	DATE	BY	CHK	APR	DESCRIPTION					ECN																
															DRAWN BY		DATE		CHK		SCALE		SIZE			
															L.VALDES		7-15-77		HVP		NONE		SHT 1 OF 1		A	