




PRODUCT-DETAILS

CP6615

Control panel. 15.6" TFT multi-touch screen, 16 M colors, 1366 x 768 pixel, Chromium Browser (CP6615)



General Information	
Extended Product Type	CP6615
Product ID	1SAP561510R0001
ABB Type Designation	CP6615
EAN	4013614529641
Catalog Description	Control panel. 15.6" TFT multi-touch screen, 16 M colors, 1366 x 768 pixel, Chromium Browser (CP6615)
Long Description	CP6615: CP600-Pro Control panel. 15.6" TFT multi-touch screen, 16 M colors, 1366 x 768 pixel, Chromium Browser. PB610 applications.

Ordering	
CN8	85371091
Invoice Description	Control panel. 15.6" TFT multi-touch screen, 16 M colors, 1366 x 768 pixel, Chromium Browser (CP6615)
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	3.33 kg
Product Net Depth / Length	64 mm
Product Net Height	267 mm
Product Net Width	422 mm
Gross Weight	4.5 kg
Package Level 1 Depth / Length	510 mm
Package Level 1 Height	145 mm
Package Level 1 Width	410 mm
Package Level 1 Units	1 carton

Certificates and Declarations	
Declaration of Conformity - CE	3ADR980149
REACH Date	20241206
REACH Declaration	3ADR980139
REACH Information	True - contains substances > 0.1 mass percentage
SCIP	cb63d514-1657-4973-82e9-9961acbb54ec Germany
RoHS Date	2018
RoHS Declaration	3ADR980149
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Technical	
Function	15.6" TFT multi-touch screen, 16 M colors, 1366 x 768 pixel, Chromium Browser
Screen Size	15.6 in
Screen Color	16000000 Colors
Screen Resolution	1366 x 768 pixel
Display Type	TFT Capacitive Multitouch
Number of Hardware Interfaces	Industrial Ethernet 3 Other 1 Parallel 0 RS-232 0 RS-422 0 RS-485 0 Serial TTY 0 USB 2 Wireless 0 PROFINET 0
Memory Size	240000 kB
Security	50
Input Voltage Type	DC
Degree of Protection	Front IP66
Supply Voltage	18 ... 32 V DC
Built-In Depth (t ₂)	56 mm
Ambient Air Temperature	Operation -20 ... +60 °C

Additional Information

Product Main Type	CP6615
Product Name	Control Panels

External Classifications and Standards	
eClass	27-33-02-01
ETIM 8	EC001412 - Graphic panel
ETIM 9	EC001412 - Graphic panel
ETIM 10	EC001412 - Graphic panel
UNSPSC	32151703

Environmental	
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
PLC Automation → Control Panels → CP600-Pro → Devices

