


WATTSTOPPER® ROOM CONTROLLER

Series Selection Quick Guide

Wattstopper room controllers are the foundation of our Digital Lighting Management (DLM) technology platform, providing integration of occupancy sensors, daylighting controls, and switches for energy-efficient lighting control. Available in a variety of options, this quick guide will help you find the best one for your space.



SERIES	LMRC-100 SERIES	LMRC-110 SERIES		LMRC-210 SERIES
		LMRC-111	LMRC-112	
DESCRIPTION	On/Off Room Controllers	Easy-to-Install, Dimming Room Controllers with Advanced Real Time Metering	Easy-to-Install, Dimming Room Controllers with Metering	Dimming Room Controller with Calculated Metering
FEATURES				
Dimming	No, On/Off only	Yes, 0-10V	Yes, 0-10V	Yes, 0-10V
Amp Capacity	20A	20A	10A	20A
Relays	1 or 2	1	2	1, 2 or 3
Voltage Metering	User Input	Automatic	User Input Automatic (-M)	User Input
Amperage Metering	User Input Max	Automatic	User Input Automatic (-M)	Automatic
Energy Monitoring/Accuracy	Calculated (on/off)	Real Time Metering (+/- 2% accuracy)	Calculated Real Time Metering (-M)	Calculated Plus (+/- 8% accuracy)
Dimming Class 1/Class 2	N/A	Class 1 or Class 2	Class 1 or Class 2	Class 2 Only
Electrical Box	Standard	Standard	Standard	Deep (4 square only)
Mounting	1/2" knock out	1/2" knock out	1/2" knock out	Facemount
IRB Power Output	150mA across 3 ports	200mA across 3 ports	150mA across 2 ports	250mA across 3 ports
MODELS AVAILABLE				
1 RELAY				
	LMRC-101	LMRC-111-20M LMRC-111-20M-U (BAA/TAA compliant)		LMRC-211 LMRC-211-347 (347VAC) LMRC-211-L24 (24" leads) LMRC-211-U (BAA/TAA compliant)
2 RELAYS				
	LMRC-102 LMRC-102-U (BAA/TAA compliant)		LMRC-112 LMRC-112-U (BAA/TAA compliant) LMRC-112-M LMRC-112-M-U (BAA/TAA compliant)	LMRC-211 LMRC-212-347 (347VAC) LMRC-212-L24 (24" leads) LMRC-212-U (BAA/TAA compliant)
3 RELAYS				
				LMRC-213 LMRC-213-347 (347VAC) LMRC-213-L24 (24" leads) LMRC-213-U (BAA/TAA compliant)