



# ENERGY STAR<sup>®</sup> exhaust fans at an economy price

## CODE compliant

ENERGY STAR<sup>®</sup> certified for permitted construction and/or Green Building Initiatives

All 60, 70 and 80 CFM exhaust fans maintain at least 50 CFM @ .25" s.p. to meet stringent codes

## VERSATILE, EASY installation



4 ways to install:

- FoldAway™ mounting ears
- Mounting flange
- Angled screws inside housing
- Hanger bars (optional accessory)

SlideClip™ Grille, easiest installation with no springs (patent pending), easier cleaning

## SEAMLESS design

Simple design that blends into the ceiling

## STREAMLINED, EASY-TO-SELECT FAN OPTIONS

| Fan | Description                        |
|-----|------------------------------------|
| BE6 | 60 CFM, 0.9 Sones Fan, CleanCover™ |
| BE8 | 80 CFM, 1.5 Sones Fan, CleanCover™ |

| Fan/Light | Description                              |
|-----------|--|
| BEL6      | 60 CFM, 0.9 Sones Fan/Light, CleanCover™ |
| BEL8      | 80 CFM, 1.5 Sones Fan/Light, CleanCover™ |

| Humidity Sensing | Description  |
|------------------|--|
| BES8             | 80 CFM, 1.5 Sones Fan, Humidity Sensing, CleanCover™       |
| BELS8            | 80 CFM, 1.5 Sones Fan/Light, Humidity Sensing, CleanCover™ |

| Bluetooth <sup>®</sup> Speaker | Description  |
|--------------------------------|--|
| BEL7A                          | 70 CFM, 2.0 Sones Fan/Light, Bluetooth <sup>®</sup> Speaker, Louvered Grille |

| Housing & Finish Packs | Description  |
|------------------------|--|
| BEH                    | Fan Only Housing Pack (6)<br>Compatible with BE6F, BE8F                            |
| BELH                   | Fan/Light Housing Pack (6)<br>Compatible with BEL6F                                |
| BE6F                   | 60 CFM, 0.9 Sones Fan, CleanCover™<br>Finish Pack (6) – Compatible with BEH        |
| BEL6F                  | 60 CFM, 0.9 Sones Fan/Light, CleanCover™<br>Finish Pack (6) – Compatible with BELH |
| BE8F                   | 80 CFM, 1.5 Sones Fan, CleanCover™<br>Finish Pack (6) – Compatible with BEH        |

| Radiation Damper | Description                   |
|------------------|-------------------------------|
| BERD             | Radiation Damper              |
| BERDWT           | Radiation Damper – Wood Truss |