




Nothing but **HEAVY DUTY.**



2022 **HOLE SAW CATALOG**



HOLE SAW SELECTION GUIDE

- 1 Identify the material to be cut in the columns below
- 2 Choose the appropriate product **RECOMMENDED** or **ACCEPTABLE**

	STAINLESS STEEL	METAL	ALUMINUM & OTHER NON-FERROUS METALS	DUCT	CAST IRON	WOOD WITH NAILS	CEILING TILE	PLASTER/ DRYWALL	PVC & PLASTICS	CLEAN WOOD	SHINGLES	FIBERGLASS	CEMENT BOARD	TILE	BRICK & BLOCK	GRANITE
HOLE SAWS	HOLE DOZER™ w/ CARBIDE TEETH															
	HOLE DOZER™ BI-METAL															
	BIG HAWG™															
	CARBIDE GRIT															
	DIAMOND MAX™															
	RECESSED LIGHT															
PILOT BITS	ADJUSTABLE HOLE CUTTER															
	SHOCKWAVE IMPACT DUTY™															
	THUNDERBOLT®															
	COBALT															

HOLE DOZER™ w/ CARBIDE TEETH HOLE SAWS

- Most Durable. LONGEST LIFE. Period.
- Longest Life in General Purpose and Extreme Materials
- Faster Cuts with 3 TPI Design

Size	Individual Package	Size	Individual Package	Size	Individual Package	Size	Individual Package
11/16"	49-56-0700	1-5/8"	49-56-0714	2-11/16"	49-56-0730	4-1/8"	49-56-0743
3/4"	49-56-0702	1-3/4"	49-56-0717	2-3/4"	49-56-0731	4-1/4"	49-56-0744
7/8"	49-56-0704	1-7/8"	49-56-0719	3"	49-56-0734	4-1/2"	49-56-0746
1"	49-56-0707	2"	49-56-0720	3-1/8"	49-56-0735	4-5/8"	49-56-0747
1-1/16"	49-56-0807	2-1/8"	49-56-0722	3-1/4"	49-56-0736	4-3/4"	49-56-0847
1-1/8"	49-56-0708	2-1/4"	49-56-0724	3-3/8"	49-56-0737	5"	49-56-0748
1-1/4"	49-56-0710	2-3/8"	49-56-0726	3-1/2"	49-56-0738	5-1/2"	49-56-0848
1-5/16"	49-56-0711	2-1/2"	49-56-0727	3-5/8"	49-56-0739	6"	49-56-0749
1-3/8"	49-56-0712	2-9/16"	49-56-0728	3-3/4"	49-56-0741		
1-1/2"	49-56-0713	2-5/8"	49-56-0729	4"	49-56-0742		

HOLE DOZER™ w/ CARBIDE TEETH HOLE SAW KITS

	9 Pc Kit 49-22-3077	9 Pc Kit 49-22-3079	10 Pc Kit 49-22-3084	12 Pc Kit 49-22-3090	12 Pc Kit 49-22-3091	15 Pc Kit 49-22-3097
Hole Saws	1-3/8", 2", 2-5/8", 3", 3-5/8", 4-1/4"	7/8", 1-1/8", 1-3/8", 2", 2-1/2"	7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2"	7/8", 1", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/4", 2-1/2"	3/4", 7/8", 1-1/8", 1-1/2", 1-3/4", 2-1/8", 2-1/4", 2-5/8"	3/4", 7/8", 1", 1-1/8", 1-1/4", 1-3/8", 1-1/2", 1-3/4", 2", 2-9/16", 3"
Arbors	49-56-7115	49-56-7115, 49-56-7110	49-56-7115, 49-56-7110	49-56-7115, 49-56-7110	49-56-7115, 49-56-7110	49-56-7115, 49-56-7110
Pilot Bits	Additional (2) 49-56-7100	Additional (2) 49-56-7100	Additional (2) 49-56-7100	Additional (2) 49-56-7100	Additional (2) 49-56-7100	Additional (2) 49-56-7100

HOLE DOZER™ w/ Carbide Teeth Hole Saw Accessories

Description	Individual Package
1/4" HOLE DOZER™ w/ Carbide Teeth Cobalt Pilot Bit	49-56-7100
HOLE DOZER™ w/ Carbide Teeth Small Hole Saw Arbor	49-56-7110
HOLE DOZER™ w/ Carbide Teeth Large Hole Saw Arbor	49-56-7115



HOLE DOZER™ BI-METAL HOLE SAWS

Size	Hanging Container	Shrink Wrap	With Arbor	Bulk	Qty
9/16"	49-56-0002	49-56-9690	–	–	–
5/8"	49-56-0012	49-56-9603	–	–	–
11/16"	49-56-0017	49-56-9604	–	–	–
3/4"	49-56-0023	49-56-9605	49-56-9658	49-56-5090	25
13/16"	49-56-0027	49-56-9606	–	–	–
7/8"	49-56-0032	49-56-9607	49-56-9659	49-56-5100	25
15/16"	49-56-0037	49-56-9608	–	–	–
1"	49-56-0043	49-56-9609	49-56-9662	49-56-5110	25
1-1/16"	49-56-0047	49-56-9610	–	–	–
1-1/8"	49-56-0052	49-56-9611	49-56-9663	49-56-5120	25
1-3/16"	49-56-0057	49-56-9612	–	49-56-5125	25
1-1/4"	49-56-0062	49-56-9613	49-56-9664	49-56-5130	25
1-5/16"	49-56-0067	49-56-9614	–	–	–
1-3/8"	49-56-0072	49-56-9615	49-56-9671	49-56-5140	25
1-7/16"	49-56-0077	49-56-9616	–	–	–
1-1/2"	49-56-0082	49-56-9617	49-56-9665	49-56-5150	25
1-9/16"	49-56-0087	49-56-9618	–	–	–
1-5/8"	49-56-0092	49-56-9619	–	49-56-5152	25
1-11/16"	49-56-0097	49-56-9620	–	–	–
1-3/4"	49-56-0102	49-56-9621	49-56-9666	49-56-5155	25
1-13/16"	49-56-0107	49-56-9622	–	–	–
1-7/8"	49-56-0112	49-56-9623	–	–	–
2"	49-56-0117	49-56-9624	49-56-9667	49-56-5160	25
2-1/16"	49-56-0122	49-56-9625	–	–	–
2-1/8"	49-56-0127	49-56-9626	49-56-9668	49-56-5165	25
2-1/4"	49-56-0132	49-56-9628	49-56-9680	49-56-5167	25
2-5/16"	49-56-0137	49-56-9629	–	–	–

Size	Hanging Container	Shrink Wrap	With Arbor	Bulk	Qty
2-3/8"	49-56-0142	49-56-9630	–	–	–
2-1/2"	49-56-0147	49-56-9631	49-56-9669	49-56-5170	25
2-9/16"	49-56-0153	49-56-9632	–	–	–
2-5/8"	49-56-0158	49-56-9633	–	49-56-5175	16
2-11/16"	49-56-0159	49-56-9634	–	49-56-5178	16
2-3/4"	49-56-0163	49-56-9635	–	–	–
2-7/8"	49-56-0167	49-56-9636	–	–	–
3"	49-56-0173	49-56-9637	49-56-9670	49-56-5180	16
3-1/8"	49-56-0177	49-56-9638	–	–	–
3-1/4"	49-56-0183	49-56-9639	–	–	–
3-3/8"	49-56-0187	49-56-9640	–	–	–
3-1/2"	49-56-0193	49-56-9641	49-56-9682	49-56-5190	9
3-5/8"	49-56-0197	49-56-9642	–	49-56-5195	9
3-3/4"	49-56-0203	49-56-9643	–	–	–
3-7/8"	49-56-0207	49-56-9644	–	–	–
4"	49-56-0213	49-56-9645	49-56-9685	49-56-5200	9
4-1/8"	49-56-0217	49-56-9646	–	49-56-5205	9
4-1/4"	49-56-0223	49-56-9647	49-56-9687	–	–
4-3/8"	49-56-0227	49-56-9648	–	–	–
4-1/2"	49-56-0233	49-56-9649	49-56-9689	–	–
4-5/8"	49-56-0239	49-56-9627	–	–	–
4-3/4"	49-56-0237	49-56-9650	–	–	–
5"	49-56-0243	49-56-9652	–	–	–
5-1/4"	49-56-0244	49-56-9653	–	–	–
5-1/2"	49-56-0247	49-56-9654	–	–	–
5-3/4"	49-56-0249	49-56-9655	–	–	–
6"	49-56-0253	49-56-9656	49-56-9698	–	–

HOLE DOZER™ BI-METAL HOLE SAW KITS

GENERAL PURPOSE					
	9 Pc Kit 49-22-4006	9 Pc Kit 49-22-4009	12 Pc Kit 49-22-4023	13 Pc Kit 49-22-4025	15 Pc Kit 49-22-4175
	Hole Saws	3/4", 7/8", 1", 1-1/8", 1-1/2"	1", 1-1/4", 1-1/2", 2", 2-1/2"	3/4", 7/8", 1", 1-1/8", 1-3/8", 1-1/2", 1-3/4", 2", 2-1/8", 2-1/2"	3/4", 7/8", 1", 1-1/8", 1-3/8", 1-1/2", 1-3/4", 2", 2-1/8", 2-1/4", 2-1/2"
	Arbors	49-56-7010	49-56-7010	49-56-7010, 49-56-7250	49-56-7010, 49-56-9100
	Pilot Bits	(2) 49-56-8010	(2) 49-56-8010	(2) 49-56-8010	Additional (2) 49-56-8010
	Other	Arbor Adapter, Adapter Washer	Arbor Adapter, Adapter Washer	Arbor Adapter, Adapter Washer, Hex Key	–

GENERAL PURPOSE					
	17 Pc Kit 49-22-4029	20 Pc Kit 49-22-4170	21 Pc Kit 49-22-4171	28 Pc Kit 49-22-4185	10 Pc Kit w/ PACKOUT™ 49-22-5606
	Hole Saws	3/4", 7/8", 1", 1-3/8", 1-1/2", 1-3/4", 2-1/8", 2-5/8", 3", 3-5/8", 4", 4-1/4", 4-1/2"	3/4", 7/8", 1", 1-1/8", 1-1/2", 2", 2-1/8", 2-1/2", 3", 3-5/8", 4-1/4", 4-1/2", 5"	3/4", 7/8", 1", 1-1/8", 1-1/4", 1-3/8", 1-1/2", 1-3/4", 2", 2-1/8", 2-1/4", 2-1/2", 2-5/8", 3", 3-1/4", 3-3/8", 3-5/8", 3-3/4", 4", 4-1/4", 4-1/2", 4-3/4"	1-1/2", 2", 2-1/2", 3", 3-5/8", 4-1/4"
	Arbors	49-56-7010, 49-56-9100	49-56-7010, 49-56-9100	49-56-7010, 49-56-7250	49-56-7010, 49-56-9100
	Pilot Bits	(5) 49-56-8010	(4) 49-56-8010	(5) 49-56-8010	Additional (2) 49-56-8010
	Other	Hex Key	Hex Key	Hex Key	–

SPECIALTY

				
	7 Pc Automotive Kit 49-22-4083	11 Pc Automotive Kit 49-22-4084	Door Lock Kit 49-22-4063	Door Lock Installation Kit 49-22-4073
Hole Saws	3/4", 7/8", 1", 1-1/8", 1-1/4"	3/4", 7/8", 1-1/8", 1-1/2", 2", 2-1/8", 2-1/4", 2-1/2"	1", 2-1/8"	1", 2-1/8"
Arbors	49-56-7010	49-56-7000, 49-56-9100	49-56-7010	49-56-7010
Pilot Bits	–	Additional 49-56-8010	49-56-8010	(2) 1/8", (2) 3/32"
Other	Arbor Adapter	–	Arbor Adapter, Spacer	Installation Guide, Adapter, Spacer, Depth Stop Insert



BIGHAWG™
CARBIDE TEETH



DIAMOND
MAX™



BIG HAWG™ w/ CARBIDE TEETH HOLE SAWS

- Cuts 1,000 More Nails
- 5X Faster Cutting
- Carbide Tipped Multi-Material Pilot Bit for Increased Material Versatility

Size	Individual Package
1-3/8"	49-56-9200
1-3/4"	49-56-9205
2-1/8"	49-56-9210
2-1/4"	49-56-9215
2-9/16"	49-56-9220

Size	Individual Package
2-3/4"	49-56-9225
3"	49-56-9230
3-5/8"	49-56-9240
4"	49-56-9245
4-1/4"	49-56-9255

Size	Individual Package
4-5/8"	49-56-9265
5-1/4"	49-56-9270
6-1/4"	49-56-9275

BIG HAWG™ w/ CARBIDE TEETH HOLE SAW KITS



	7 Pc Kit 49-56-9280	8 Pc Kit 49-56-9285	9 Pc Kit with PACKOUT™ Compact Organizer 49-56-9295	10 Pc Kit 49-56-9290
Hole Saws	2-1/8", 2-9/16", 3-5/8"	2-1/8", 2-9/16", 3-5/8", 4-5/8"	2-1/8", 2-9/16", 3", 3-5/8", 4-5/8"	2-1/8", 2-1/4", 2-9/16", 3", 3-5/8", 4-1/4"
Arbors	49-56-9305	49-56-9305	49-56-9305	49-56-9305
Pilot Bits	Additional (2) 48-27-1401	Additional (2) 48-27-1401	Additional (2) 48-27-1401	Additional (2) 48-27-1401
Other	Diamond File, Hex Key	Diamond File, Hex Key	PACKOUT™ Compact Organizer	Diamond File, Hex Key

BIG HAWG™ w/ Carbide Teeth
Hole Saw Accessories

Description	Individual Package
BIG HAWG™ w/ Carbide Teeth Diamond File	48-09-5055
BIG HAWG™ w/ Carbide Teeth Multi-Material Pilot Bit	49-56-9300
BIG HAWG™ w/ Carbide Teeth Arbor	49-56-9305
BIG HAWG™ w/ Carbide Teeth Clean Wood Pilot Bit	48-27-1401

DIAMOND MAX™ DIAMOND GRIT HOLE SAWS



UP TO
10x LIFE

IDEAL FOR
PORCELAIN

DIAMOND MAX™ Hole Saw Kits



	3 Pc Kit 49-56-0500	2 Pc Kit 49-56-0501
Hole Saws	3/16", 1/4", 5/16"	(2) 1/4"



One-Piece
Hole Saws

Size	Individual Package
3/16"	49-56-0503
1/4"	49-56-0505
5/16"	49-56-0507
3/8"	49-56-0509
1/2"	49-56-0511
5/8"	49-56-0513
3/4"	49-56-0515
1"	49-56-0517



Threaded
Hole Saws

Size	Individual Package
7/8"	49-56-5605
1-1/8"	49-56-5615
1-1/4"	49-56-5620
1-3/8"	49-56-5625
1-1/2"	49-56-5630
2"	49-56-5645
2-1/2"	49-56-5660

Threaded Hole Saw Accessories



Description	Individual Package
Large Arbor w/ Retractable Starter Bit (1-1/4" and Larger)	49-56-7135
Retractable Starter Bit	49-56-8025
Angle Grinder Adapter (7/8" to 1-1/8")	49-56-7103
Angle Grinder Adapter (1-1/4" and Larger)	49-56-7105

SHOCKWAVE IMPACT DUTY™ HOLE SAWS

SHOCKWAVE
IMPACT DUTY



- Ejection Spring Automatically Removes Slugs
- Thin Wall 8 TPI for Fast, Burr-Free Holes
- Stop Shoulder Prevents Over-Drilling
- 1/4" Hex Shank for Use in Impact Drivers

Size	Individual Package	Size	Individual Package
3/4"	49-56-9805	1-1/4"	49-56-9825
7/8"	49-56-9810	1-3/8"	49-56-9830
1"	49-56-9815	1-1/2"	49-56-9835
1-1/8"	49-56-9820		

SHOCKWAVE® Impact Duty™ Hole Saw Kit



	3 Pc Kit 49-22-4800
Hole Saws	7/8", 1-1/8", 1-3/8"

CARBIDE GRIT HOLE SAWS




- Coarse Grit & Segmented Edge for Fast Cutting
- Wide, Angled & Offset Slots for Easy Plug Removal

Size	Individual Package
3/4"	49-56-0405
7/8"	49-56-0409
1"	49-56-0413
1-1/8"	49-56-0417
1-1/4"	49-56-0422
1-3/8"	49-56-0426
1-3/4"	49-56-0437
2"	49-56-0444
2-1/4"	49-56-0449
2-1/2"	49-56-0456

All sizes include carbide tipped pilot bit.

RECESSED LIGHT HOLE SAWS

ADJUSTABLE



- Debris Shield Collar
- Tool-Free Adjustability (2" - 7")

CONTINUOUS GRIT



- Continuous Grit Edge for Smooth Cuts
- Open Back for Easy Plug Removal
- Solid, Welded Construction for Accurate Hole Sizes

Description	Individual Package
Adjustable Hole Cutter (2" - 7")	49-56-0320
Adjustable Hole Cutter Replacement Blades and Pilot Bit	49-56-0290

Size	Description	Individual Package
3-1/8"	Recessed Light Hole Saw	49-56-0296
4-3/8"	Recessed Light Hole Saw	49-56-0300
5-3/8"	Recessed Light Hole Saw	49-56-0303
6-3/8"	Recessed Light Hole Saw	49-56-0305
6-5/8"	Recessed Light Hole Saw	49-56-0310
6-7/8"	Recessed Light Hole Saw	49-56-0315

All sizes include pilot bit.

HOLE SAW CASES ONLY

COMPLETE CUSTOMIZATION

SMALL



	Small Hole Saw Case* 49-56-1006
Includes	Removable Accessory Box, 7 Interchangeable Pegs



*Fits in PACKOUT™ Organizers

LARGE



	Large Hole Saw Case** 49-56-1007
Includes	Removable Accessory Box, 6 Interchangeable Pegs

**BIG HAWG™ is only compatible with the large case

- FOLD UNDER LID Fast and Easy Access
- TOP AND BOTTOM REINFORCED GRID To Keep Hole Saws Securely Stored
- REMOVABLE ACCESSORY BOX For Arbors, Pilot Bits, & More
- NEW HEAVY DUTY LATCH
- WEBBED HANDLE DESIGN More Flexible Carrying Positions
- INTERCHANGEABLE PEGS Multiple Kit Configurations

COMPATIBLE WITH







PILOT BITS

- THUNDERBOLT® Pilot Bit with Thicker Core - Up To 5X More Durable



Description	Individual Package	Bulk	Qty
1/4" x 4" THUNDERBOLT® Pilot Bit	49-56-8000	49-56-8031	12
1/4" x 3-1/2" THUNDERBOLT® Pilot Bit	49-56-8010	49-56-8033	12
1/4" x 4" Carbide Tipped Pilot Bit	49-56-8005	-	-
1/4" HOLE DOZER™ w/ Carbide Teeth Cobalt Pilot Bit	49-56-7100	-	1
HOLE DOZER™ w/ Carbide Teeth Small Hole Saw Arbor	49-56-7110	-	1
HOLE DOZER™ w/ Carbide Teeth Large Hole Saw Arbor	49-56-7115	-	1

HOLE SAW ARBORS

- UNIVERSAL

 - Works with all major brands of hole saws
 - Accepts any 1/4" straight or 3-flat shank pilot bit
- DURABLE

 - Made from hardened steel and alloy steel
- QUICK CHANGE ARBORS

 - Tool-free operation
 - No adapter required

								
Hole Saw Size Range	Up to 1-3/16" Hole Saw			1-1/4" & Larger Hole Saw				
Model Number	49-56-7010	49-56-7000	49-56-6950	49-56-7040	49-56-7055	49-56-9100	49-56-7250	49-56-7240
Minimum Chuck Size	3/8"	1/2"	1/4"	3/8"	1/2"	1/2"	3/8"	1/2"
Style	-	-	-	-	Quick Change	Quick Change	Quick Change	Quick Change

EXTENSIONS AND ADAPTERS

- Universal Fit - All Extensions Work With All Major Brands



Description	Minimum Chuck Size	Individual Package
3/8" x 12" Bit Extension	3/8"	48-28-4008
3/8" x 6" Universal QUIK-LOK™ Extension	3/8"	48-28-2010
3/8" x 12" Universal QUIK-LOK™ Extension	3/8"	48-28-2020
3/8" x 18" Universal QUIK-LOK™ Extension	3/8"	48-28-2030
3/8" x 24" Universal QUIK-LOK™ Extension	3/8"	48-28-2040

Description	Minimum Chuck Size	Individual Package
7/16" x 5-1/2" Bit Extension	1/2"	48-28-4001
7/16" x 12" Bit Extension	1/2"	48-28-4006
7/16" x 18" Bit Extension	1/2"	48-28-4011
7/16" x 24" Bit Extension	1/2"	48-28-4016
7/16" x 5-1/2" QUIK-LOK™ Extension	1/2"	48-28-1030
7/16" x 12" QUIK-LOK™ Extension	1/2"	48-28-1040
7/16" x 18" QUIK-LOK™ Extension	1/2"	48-28-1050
7/16" x 24" QUIK-LOK™ Extension	1/2"	48-28-1060
Adapter Spacer	-	49-67-0120
Arbor Adapter	-	49-56-6560

FULL COMPATIBILITY FROM TOOL TO ACCESSORY

3/8" Universal QUIK-LOK™ Extensions



Description	Individual Package
6" x 3/8" Universal QUIK-LOK™ Extension	48-28-2010
12" x 3/8" Universal QUIK-LOK™ Extension	48-28-2020
18" x 3/8" Universal QUIK-LOK™ Extension	48-28-2030
24" x 3/8" Universal QUIK-LOK™ Extension	48-28-2040

7/16" Universal QUIK-LOK™ Extensions



Description	Individual Package
5-1/2" x 7/16" Universal QUIK-LOK™ Extension	48-28-1030
12" x 7/16" Universal QUIK-LOK™ Extension	48-28-1040
18" x 7/16" Universal QUIK-LOK™ Extension	48-28-1050
24" x 7/16" Universal QUIK-LOK™ Extension	48-28-1060



Nothing but **HEAVY DUTY.**



MADE IN USA
WITH GLOBAL MATERIALS