

NON-METALLIC BOXES and EXTENSION RINGS





SPB2001R



SPB2002R



SPB2003R



SPB2008R

Cat. No.	Volume (Cu. In.)	Description	Products Size L×W×D	Ctn. Box Size L×W×D(cm)	Std. Ctn. Qty.
One, Two and Three Gang					
SPB2001R	18.0	One-gang plastic device box, For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 2 green screws.	3-3/4"×2-1/4"×2-3/4"	37×34×26	50
SPB2002R	37.0	Two-gang plastic device box, For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 2 green screws.	3-3/4"×4"×2-3/4"	56.5×37×24.5	50
SPB2003R	51.0	Three-gang plastic device box, For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 3 green screws.	3-3/4"×5-3/4"×2-3/4"	54.5×33.5×22.5	30
Octagon Box					
SPB2008R	26.0	Octagon plastic device box, For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 2 green screws.	4"×3-3/4"×2-3/4"	54.5×39×24	50



Cat. No.	Volume (Cu. In.)	Description	Products Size L×W×D	Outer Box Size L×W×D(cm)	Std. Ctn. Qty.
Vapor Proof One, Two, Three and Four Gang					
SPB2001VB	18.0	One-gang plastic device box, with vapour barrier. For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 2 green screws	3-3/4"×2-1/4"×2-3/4"	39.5×38.5×27.5	50
SPB2002VB	37.0	Two-gang plastic device box, with vapour barrier. For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 2 green screws.	3-3/4"×4"×2-3/4"	61.5×38.5×26.5	50
SPB2003VB	51.0	Three-gang plastic device box, with vapour barrier. For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 3 green screws.	3-3/4"×5-3/4"×2-3/4"	61.5×39.5×24.5	30
SPB2004VB	67.0	Four-gang plastic device box, with vapour barrier. For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 4 green screws.	3-7/10"×7-3/4"×2-3/4"	46.5×43×37	30
Vapor Proof Dryer Box & Octagon Box					
SPB2005VB	61.0	Dryer plastic box, with vapour barrier. For non metallic sheathed cable, 10AWG-8AWG. With grounding plate, 1 green screws.	5"×5"×2-3/4"	42×40.5×31	30
SPB2008VB	26.0	Octagon plastic device box, with vapour barrier. For non metallic sheathed cable, 16AWG-10AWG. With grounding plate, 2 green screws.	4"×3-3/4"×2-3/4"	61.5×38.5×26.5	50


EXTENSION RING



SBE1



SBE2



SBE3



SBE8

Cat. No.	Description	Products Size L×W×D	Outer Box Size L×W×D(cm)	Std. Ctn. Qty.
One, Two, and Three Gang				
SBE1	Single Gang Electrical Outlet Box Extender	2.43"×4.28"×1.85"	64×45×26.5	400
SBE2	Two Gang Electrical Outlet Box Extender	4.32"×4.28"×1.85"	64×45×26.5	200
SBE3	Three Gang Electrical Outlet Box Extender	6.13"×4.28"×1.85"	64×43×37	200
Ceiling Box				
SBE8	Ceiling Box Extender/Set Back Ceilings	4.92"×4.92"×1.50"	64×43×38	200