

## EZ-RJ45™ Cat 6 Plug and Crimp Tool

### APPLICATION

The EZ-RJ45 Cat 6 Plug and Crimp Tool provides quick, cost-effective UTP wire terminations. The plug features openings that allow wires to be inserted and extended out of the front, providing increased performance, wire sequence verification, and no wasted connectors, crimps, or bad terminations. The crimp tool features a built-in cutter and stripper that crimps and cuts wires in one operation. It accommodates EZ-RJ45 plugs, and most standard RJ-45 and RJ-11 plugs. This craft-friendly tool features precision ground-crimp dies, a full-cycle ratcheting mechanism, and steel construction for strength and durability.



EZ-RJ45 Cat 6 Plug



Required Tool: EZ-RJ45 Crimp Tool

### FEATURES

- Clear housing for wire sequence verification
- Plug opening allows cables to feed through for crimp precision

### DESIGN CONSIDERATIONS

- 8-conductor modular plug
- For insulated conductors with OD range of 0.037" to 0.042" (0.94 mm to 1.07 mm)
- Max cable OD: 0.275" (6.985 mm)
- Insert/extraction life: 1000 cycles
- Terminates both solid and stranded cable
- After installation, test the connector-plug link using the method for a Modular Plug Terminated Link, as described in ANSI/TIA-568.2-D
- Ideal for use with indoor LSZH, CM, CMR, and CMP cable constructions. For Outside Plant (OSP) and Industrial cable constructions evaluate plug and cable combination for application suitability

### STANDARDS & REGULATIONS

- ANSI/TIA-568.2-D (CAT 6)

### MECHANICAL SPECIFICATIONS

Dimensions: See page two  
 Materials: Polycarbonate body  
 Phosphor bronze contacts

### COUNTRY OF ORIGIN

CAT 6 Plug: USA  
 Crimp Tool: Taiwan


### WARRANTY INFORMATION

For Leviton product warranties, go to [leviton.com/ns/warranty](http://leviton.com/ns/warranty)

47613-EZ6, 40989-ACT

**PRODUCT SPECIFICATIONS**  
**47613-EZ6, 40989-ACT**

47613-EZ6, 40989-ACT



PART NUMBERS	
Description	Part No.
EZ-RJ45™ Cat 6 Plug	47613-EZ6
EZ-RJ45 Crimp Tool	40989-ACT

For further support information, visit [leviton.com/ns/support](http://leviton.com/ns/support)  
 EZ-RJ45 is a trademark of SullStar Technologies, Inc.

Page 2 of 2

**USA**  
 Network Solutions Headquarters  
 +1 (800) 722 2082  
[infoUSA@leviton.com](mailto:infoUSA@leviton.com)  
 Leviton Berk-Tek Cable: +1 (800) 237 5835  
[berktek.info@leviton.com](mailto:berktek.info@leviton.com)

**Asia Pacific**  
 +852 3620 2602  
[infoAPAC@leviton.com](mailto:infoAPAC@leviton.com)

**Canada**  
 +1 (800) 461 2002  
[infoCanada@leviton.com](mailto:infoCanada@leviton.com)

**Europe**  
 +44 (0) 1592 772124  
[infoEurope@leviton.com](mailto:infoEurope@leviton.com)

**Latin America**  
 MX: +52 (55) 2128 6286  
 LATAM: +52 (55) 2333 5963  
[infoLATAM@leviton.com](mailto:infoLATAM@leviton.com)

**Middle East & Africa**  
 +971 (4) 247 9800  
[infoMEA@leviton.com](mailto:infoMEA@leviton.com)

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT [LEVITON.COM/NS](http://LEVITON.COM/NS) TO LEARN MORE.