

MX FUEL™ CARRY-ON™ 3600W/1800W
Power Supply Kit

POWER
MORE
ON DEMAND

PORTABLE
POWER
ANYWHERE

MORE
EFFICIENT
POWER

MXF002-2XC
Specifications:

Peak Watts	3,600W
Running Watts	1,800W
Outlets	(2) 120V 15A Outlets
Inverter Output	Pure Sine Wave
Integrated Charger	Yes
Push Button Start	Yes
ONE-KEY™ Compatible	Track and Manage.
Ground Fault Isolated	Yes
Intended For	One 15 Amp Tool
Battery Compatibility	Fits All MX FUEL™ Battery Packs
Warranty	2 Year Equipment and Battery

Includes: (2) MX FUEL™ REDLITHIUM™
XC406 Battery Packs, Detachable Charger Cord

GROUND
FAULT
ISOLATED



MX FUEL™ ROCKET™ Tower
Light/Charger Kit

MOST
PORTABLE
10' LIGHT
INSIDE / OUTSIDE

27,000
LUMENS OF
TASK OR AREA LIGHTING

WITHSTANDS
THE STORM

MXF041-1XC
Specifications:

Max Lumens	27,000
Modes	High / Medium / Low
Collapsed Height	44"
Extended Height	10'
Width	20.8"
Depth	24.8"
Weight w/ Battery	110 lbs
Ingress Rating	Outdoor Use
Push Button Start	Yes
ONE-KEY™ Compatible	Customize. Track. Manage.
Battery Compatibility	Fits All MX FUEL™ Battery Packs
Warranty	2 Year Equipment and Battery

Includes: (1) MX FUEL™ REDLITHIUM™
XC406 Battery Pack



MX FUEL™ Sewer Drum Machine
w/ POWERTREDZ™ Kit

POWERTREDZ™
LIFT ASSIST

POWER
TO CLEAR
ROOTS AT 200'

MESS
CONTAINED

MXF501-1CP
Specifications:

Drain Line Capacity	3" – 8" up to 200'
Drum Capacity	100'
Cable Capacity	5/8" and 3/4"
Powered Cable Feed & Retract	Yes, CABLE DRIVE™
Cable Spin Speed	200 RPM
Height / Length	47" / 32.5"
Weight w/ Battery	125 lbs
Lift Assist	Yes, POWERTREDZ™
Push Button Start	Yes
ONE-KEY™ Compatible	Track and Manage.
Battery Compatibility	Fits All MX FUEL™ Battery Packs
Warranty	2 Year Equipment, Battery & Charger

Includes: (1) MX FUEL™ REDLITHIUM™ CP203 Battery Pack,
MX FUEL™ Charger, 3/4" Anchor Cable



MX FUEL™ Sewer Drum
Machine Accessories

Compatible with MXF501-1CP, MXF500-1CP

Machine Accessories
47-53-5001 6-1/2" Guide Hose
47-53-5002 Load Wheel

**5/8" Inner
Core Cables**
48-53-2325 – 25'
48-53-2350 – 50'
48-53-2310 – 100'

**3/4" Inner
Core Cables**
48-53-2425 – 25'
48-53-2450 – 50'
48-53-2410 – 100'
**Leader Cables &
Anchor Cable**
48-53-2802 Leader Cable
48-53-2902 Leader Cable
48-53-2905 Anchor Cable

**Cable Head
Attachments**
48-53-2830 Straight Auger
48-53-2831 Funnel Auger
48-53-2835 Small Opening Tool
48-53-2836 Medium Opening Tool
48-53-2832 3" Root Cutters
48-53-2833 4" Root Cutters
48-53-2834 6" Root Cutters
48-53-2837 3" Grease Cutters
48-53-2838 4" Grease Cutters
48-53-2829 Pin Key
48-53-2839 Case
48-53-2840 9 pc Cable Head
Attachment Kit

Also Available:

MX FUEL™ Sewer Drum Machine Kit
MXF500-1CP

Specifications:

Drain Line Capacity	3" – 8" up to 200'
Drum Capacity	100'
Cable Capacity	5/8" and 3/4"
Powered Cable Feed & Retract	Yes, CABLE DRIVE™
Cable Spin Speed	200 RPM
Height / Length	47" / 32.5"
Weight w/ Battery	110 lbs
Lift Assist	No
Push Button Start	Yes
ONE-KEY™ Compatible	Track and Manage.
Battery Compatibility	Fits All MX FUEL™ Battery Packs
Warranty	2 Year Equipment, Battery & Charger

Includes: (1) MX FUEL™ REDLITHIUM™ CP203 Battery Pack,
MX FUEL™ Charger, 3/4" Anchor Cable



MX FUEL™ Backpack Concrete Vibrator Kit

POWER TO PUSH 2.5" HEAD

NO GAS HEADACHES

70 YDS³ PER CHARGE, 1-1/2" HEAD, 7' WHIP

MXF371-2XC

Specifications:

Maximum Head Size	2-1/2"
Maximum Shaft Length	21 ft
Quick Connect	Yes
Weight w/ Battery	34.5 lbs
Push Button Start	Yes
Removable Harness	Yes
ONE-KEY™ Compatible	Track and Manage.
Battery Compatibility	Fits All MX FUEL™ Batteries
Wireless Remote Included	Yes
Compatible w/ Oztec	Yes
Warranty	2 Year Equipment, Battery & Charger

Includes: (2) MX FUEL™ REDLITHIUM™ XC406 Battery Packs, MX FUEL™ Charger, MX FUEL™ Concrete Vibrator Remote

Available Accessories:

(Not Included)

48-37-5015
1-1/2" Head

48-37-7007
7' Shaft

48-37-5020
2" Head

48-37-7014
14' Shaft

MX FUEL™ Vibratory Screed Kit

POWER TO PULL 16' BAR

NO GAS HEADACHES

2 HOURS PER CHARGE, w/ 12' BAR

MXF381-2CP

Specifications:

VPM	4,000 – 9,000
Bar Range	4 – 16 ft
Adjustable Handlebars	Yes
Kickstand	Yes
Weight w/ Battery	37 lbs
Push Button Start	Yes
ONE-KEY™ Compatible	Track and Manage.
Battery Compatibility	Fits All MX FUEL™ Battery Packs
Compatible w/ MBW Bars	Yes
Warranty	2 Year Equipment, Battery & Charger

Includes: (2) MX FUEL™ REDLITHIUM™ CP203 Battery Packs, MX FUEL™ Charger, (1) 9/16 Wrench

Available Accessories:

(Not Included)

48-38-2016 16 ft Screed Bar
48-38-2014 14 ft Screed Bar
48-38-2012 12 ft Screed Bar
48-38-2010 10 ft Screed Bar
48-38-2008 8 ft Screed Bar
48-38-2006 6 ft Screed Bar
48-38-2004 4 ft Screed Bar

MX FUEL™ Batteries and Charger

MX FUEL™ REDLITHIUM™ XC406 Battery

MXFXC406

Specifications:

Compatibility	Fits All MX FUEL™ Equipment
Charge Duration	90 min
Capacity	6.0 Ah
Fuel Gauge	Yes
REDLINK™ Intelligence	Yes
ONE-KEY™ Compatible	Yes
Warranty	2 Year

MX FUEL™ REDLITHIUM™ CP203 Battery

MXFCP203

Specifications:

Compatibility	Fits All MX FUEL™ Equipment
Charge Duration	45 min
Capacity	3.0 Ah
Fuel Gauge	Yes
REDLINK™ Intelligence	Yes
ONE-KEY™ Compatible	No
Warranty	2 Year

MX FUEL™ REDLITHIUM™ XC406 Battery/Charger Expansion Kit

MXFC-2XC

Includes: (2) MX FUEL™ REDLITHIUM™ XC406 Battery Packs, MX FUEL™ Charger

MX FUEL™ Charger

MXFC

Specifications:

Compatibility	Charges All MX FUEL™ Batteries
Charge Speed	Charges MX FUEL™ CP203 Battery in 45 min Charges MX FUEL™ XC406 Battery in 90 min
REDLINK™ Intelligence	Yes
On-Board Fan	Yes
Cell Voltage Monitoring	Yes
On-Board Indicator Light	Yes
Warranty	2 Year

LEARN MORE



NEW

ONE-KEY™ BLUETOOTH TRACKING TAG

AVAILABLE IN

1 PC
48-21-2301

2 PC
48-21-2302

10 PC
48-21-2310

TRACKED BY ONE-KEY

DOWNLOAD THE FREE APP NOW!



Apple, the Apple logo and iBeacon are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Google Play and the Google Play logo are trademarks of Google Inc.

The Bluetooth® word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Milwaukee Tool is under license. Other trademarks and trade names are those of their respective owners.

