




SWITCHBLADE™ SELFEE BITS

Description	Part No.	Description	Part No.
1-3/8" SWITCHBLADE™ Selfeed Bit	48-25-5120	2-1/8" SWITCHBLADE™ Selfeed Bit	48-25-5140
1-1/2" SWITCHBLADE™ Selfeed Bit	48-25-5125	2-1/4" SWITCHBLADE™ Selfeed Bit	48-25-5143
2" SWITCHBLADE™ Selfeed Bit	48-25-5135	2-9/16" SWITCHBLADE™ Selfeed Bit	48-25-5150

SWITCHBLADE™ SELFEE BIT KIT

SWITCHBLADE™ SELFEE BIT KIT

Description	Includes	Part No.
 5 PC SWITCHBLADE™ Selfeed Bit Plumber's Kit	(1) 1-3/8" SWITCHBLADE™ Selfeed Bit (1) 1-1/2" SWITCHBLADE™ Selfeed Bit (1) 2-1/8" SWITCHBLADE™ Selfeed Bit (1) 2-9/16" SWITCHBLADE™ Selfeed Bit (1) 7/16" x 5-1/2" QUIK-LOK™ Extension (1) Hex Wrench	49-22-5100

SWITCHBLADE™ SELFEE BIT COMPATIBILITY

SWITCHBLADE™ SELFEE BIT COMPATIBILITY

Size	1 PC	3 PC	3" Blade Replacement Kit	10 PC Blade Replacement Kit	Replacement Feed Screw Kit	SWITCHBLADE™ Feed Screw Kit
1-3/8"	48-25-5420	48-25-5520	48-25-5220	48-25-5320	48-25-5275	48-25-5280
1-1/2"	48-25-5425	48-25-5525	48-25-5225	48-25-5325		
2"	48-25-5435	48-25-5535	48-25-5235	48-25-5335		
2-1/8"	48-25-5440	48-25-5540	48-25-5240	48-25-5340		
2-1/4"	48-25-5443	48-25-5543	48-25-5243	48-25-5343		
2-9/16"	48-25-5450	48-25-5550	48-25-5250	48-25-5350		

SHOCKWAVE IMPACT DUTY™ LINEMAN'S AUGER BITS



OVERVIEW

The SHOCKWAVE Impact Duty™ Lineman's Auger Bits are engineered to deliver cleaner, faster holes in wooden utility poles. They feature a single-spur design, which scores the edge of the hole, creating a cleaner finish that allows bolts to slide through without resistance. The bits are coated with a reinforced anti-friction PTFE coating for overall smoother drilling and easier removal of the bit from the pole. The aggressive feed screw and cutting edge pull the bit through the material while the optimized wide flute geometry quickly ejects the chips to clear the hole and reduce clogs, leading to overall faster drilling speeds.

FEATURES

- Engineered for the power utility lineman to drill cleaner, faster holes in wooden utility poles
- Single-Spur Design: Scores the hole for a cleaner finish
- Reinforced Anti-Friction PTFE Coating: Overall smoother drilling

SHOCKWAVE IMPACT DUTY™ LINEMAN'S AUGER BITS

Description	18" Part No.	24" Part No.	30" Part No.
3/8" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6700	48-13-6800	–
1/2" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6702	48-13-6802	–
9/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6703	48-13-6803	–
5/8" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6704	48-13-6804	48-13-6904
11/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6705	48-13-6805	48-13-6905
13/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6707	48-13-6807	48-13-6907
15/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6709	48-13-6809	48-13-6909
1" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6710	48-13-6810	–
1-1/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6711	48-13-6811	–
1-1/8" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6712	48-13-6812	–
1-1/4" SHOCKWAVE Impact Duty™ Lineman's Auger Bit	48-13-6713	48-13-6813	–
11/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bits (25 pk)	48-13-6795	–	–
13/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bits (25 pk)	48-13-6797	–	–
15/16" SHOCKWAVE Impact Duty™ Lineman's Auger Bits (25 pk)	48-13-6799	–	–