

Series Spec Sheet

CIRKA DECO

5" CYLINDER MOUNTING KIT ACCESSORIES

Surface or Suspended

FEATURES AND SPECIFICATIONS

• Construction

Physical Characteristics

- Metal housing available in white or black finish
- Available cylinder size: 5"
- Compatible luminaire (order separately): 70672
([click here for full luminaire specifications](#))

Mounting

- Surface or suspended installation (see mounting kit accessories)
- For suspended installations, cable length is 10' standard (field adjustable)

Sleek Modern Design

- Clean cylindrical profile that adds a refined decorative touch to any space

Versatile Applications

- Available as individual or multi-cylinder, these mounting kit accessories will suit both smaller and larger spaces
- Ideal for both residential and commercial environments, including kitchens, dining areas, reception spaces, boutiques, and hospitality settings



quick
ship

5^{yrs}
warranty



ICES
005



CYLINDER MOUNTING KIT ACCESSORIES¹

Order Code	Model Number	Diameter (in.)	Cable Length (in.)	Finish	Compatible Luminaire (not included)	Master Case Qty	UPC
Surface Cylinder							
70658	5IN CYL SURFACE KIT BLACK FOR CLCR5	5 3/8	-	Black	70672	20	069549036369
70659	5IN CYL SURFACE KIT WHITE FOR CLCR5	5 3/8	-	White	70672	20	069549036376
Suspended Individual Cylinder							
70660	5IN CYL 10FT SUSP KIT BLACK FOR CLCR5	5 3/8	120	Black	70672	16	069549036383
70661	5IN CYL 10FT SUSP KIT WHITE FOR CLCR5	5 3/8	120	White	70672	16	069549036390
Suspended Multi-Cylinder							
70662	MULTI CYL 10FT SUSP KIT BLACK FOR CLCR5	5 3/8	120	Black	3x 70672	1	069549036406
70663	MULTI CYL 10FT SUSP KIT WHITE FOR CLCR5	5 3/8	120	White	3x 70672	1	069549036413

¹ Compatible luminaire is not included in mounting kit accessory and needs to be ordered separately (see compatible luminaire table)

COMPATIBLE LUMINAIRE (order separately) 

Order Code	Model Number	Watts (W)	Lumen Output (lm) ^{2,3}	Efficacy (lm/W)	Color Temp. (K) ¹
70672	CLCR5-R11W-A-5CWH	11	910	83	2 700/3 000/3 500/4 000/5 000

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %.


³ Lumen values are based on 3 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.

Pair the CIRKA DECO luminaire with the cylinder mounting kit accessory for a decorative look that fits any space.


SURFACE MOUNT



SUSPENDED MOUNT INDIVIDUAL CYLINDER




MULTI-CYLINDER




Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

DIMENSIONS AND WEIGHTS


Surface



Suspended - Individual Cylinder



Suspended - Multi-Cylinder



	Surface	Suspended - Individual Cylinder	Suspended - Multi-Cylinder
Net weight (lbs)	0.78	1.48	5.07

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.