


Nonmetallic - Cable tray systems

Drop outs and barrier strips




Ladder drop out

Specially designed ladder drop outs provide a rounded surface with adequate radius to protect cable as it exits from the tray, preventing damage to insulation.

Cat. No.	Material
NM-XDOP1104-W*	Pultruded fiberglass


* Supplied with a 4in. Radius
W = Tray width.

Barriers



Cat. No.	Material	Side rail height (in.)	Side rail height (mm)
NM-BS08P-120	Polyester resin	8	203.2
NM-BS06P-120	Polyester resin	6	152.4
NM-BS04P-120	Polyester resin	4	101.6
NM-BS03P-120	Polyester resin	3	76.2
NM-BS08V-120	Vinylester resin	8	203.2
NM-BS06V-120	Vinylester resin	6	152.4
NM-BS04V-120	Vinylester resin	4	101.6
NM-BS03V-120	Vinylester resin	3	76.2

Barriers are provided in 10 ft. lengths and supplied for field installation using 3/16" SS rivets (ref. part # TPDR) or use of an adjustable clamp ref. part # XXX (for 3, 4, 6 and 8" deep ladder tray).



Flexible horizontal barrier kit

Kit contents


- 1 pc. 72" (1,828.8mm) straight barrier
- 4 pc. XF-9002 barrier strip clip
- 8 pc. SS6 pop rivets
- 4 pc. #10 x 3/4" stainless steel self-tapping screw
- Assembly required - directions included

Cat. No.	Material	Side rail height (in.)	Side rail height (mm)	Loading depth (in.)	Loading depth (mm)
NM-BS08P-90HBFL	Polyester resin	8	203.2	6 ¹¹ / ₁₆	169.86
NM-BS06P-90HBFL	Polyester resin	6	152.4	4 ¹¹ / ₁₆	119.06
NM-BS04P-90HBFL	Polyester resin	4	101.6	2 ¹¹ / ₁₆	68.26
NM-BS03P-90HBFL	Polyester resin	3	76.2	1 ³ / ₄	44.45
NM-BS08V-90HBFL	Vinylester resin	8	203.2	6 ¹¹ / ₁₆	169.86
NM-BS06V-90HBFL	Vinylester resin	6	152.4	4 ¹¹ / ₁₆	169.86
NM-BS04V-90HBFL	Vinylester resin	4	101.6	2 ¹¹ / ₁₆	68.26
NM-BS03V-90HBFL	Vinylester resin	3	76.2	1 ³ / ₄	44.45

One kit allows up to 38 (965.2mm) radius position of the barrier.
For larger than 38 (965.2mm) radius barrier position, two kits are required.

Nonmetallic - Cable tray

Accessories




Heavy-duty cover clamp

- Recommended for outdoor service
- Heavy-duty cover clamp available for flat covers only
- Available in stainless steel only

Cat. No.	Material	Side rail width (in.)	Side rail width (mm)
NM-XWC-P-08-9034	Stainless steel	8	203.2
NM-XWC-P-W6-9034		6	152.4
NM-XWC-P-04-9034		4	101.6
NM-XWC-P-03-9034		3	76.2

Pop rivets

	Cat. No.	Material
	TPDR	Stainless steel
		Thermoplastic

Raised cover clamps available.
Please consult your ABB representative.



Kit contents

- Resin
- Catalyst
- Stir stick and applicator

Brush-on resin seal kit

Cat. No.	Description
NM-RSK-QT	946 ml

To reseal fiberglass after field modifications.
Vinylester resin.