

PHILIPS

**13PAR38/COR/930/F25/D
IM/P/ULW/T20 6/1FB**

929003737104



CorePro, LEDspot, PAR38, dimmable, 120 W, E26, 3000 K, 1300 lm, 25000 hour(s), Plastic

CorePro, LEDspot, PAR38, dimmable, 120 W, E26, 3000 K, 1300 lm, 25000 hour(s), Plastic, 100 lm/W

General Information

Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot

Light Technical

Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)

Luminous Flux	1,300 lm
Luminous Intensity (Nom)	6,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	60 Hz
Power Consumption	13 W
Lamp Current (Nom)	150 mA
Wattage Equivalent	120 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature

T-Case Maximum (Nom)	85 °C
----------------------	-------


Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR38
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.150 kg

Dimensional drawing



Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-40 to +45 °C

Application Conditions


can it be used in closed luminares	Yes
Wireless Technology	Not applicable

Product Data


Order product name	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB
Full product name	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB
Order code	929003737104
Material Nr. (12NC)	929003737104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677586133
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677586138

Product	D	C
13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm

Photometric data




Light Distribution Diagram -
13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB




Spectral Power Distribution Colour -
13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram -
13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB

Related Documents

Documents and certificates	Document Name	Download
Environmental Product Declaration	EPD-Philips-LED-PAR38-COMF-7403300-Plastic-COMF-7403300-Ref-929003738104-EPD.pdf	Download
Photometry and lighting design	Document Name	Download
IES File	LEDspots-COR-NAM-13W-PAR38-E26-930-25D-1-A-IES.ies	Download

