

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Series Spec Sheet

CIRKA DECO

DECORATIVE PENDANT MOUNTING KIT ACCESSORIES

Cone and Dome Styles

FEATURES AND SPECIFICATIONS

• Construction

Physical Characteristics

- Metal shade available in white or black finish
- Available in cone or dome shapes
- Compatible luminaires (order separately):
 - 15" dome and 16" cone: compatible luminaire is 70674 (CLCR9 R18W-A-5CWH)
 - 18" dome and 19" cone: compatible luminaire is 70675 (CLCR12-R24W-A-5CWH)
 - [Click here for full luminaire specifications](#)

Mounting

- Suspended installation (see mounting kit accessories)
- Cable length is 10' standard (field adjustable)

Sleek Modern Design

- Refined cone and dome silhouettes to create a timeless yet modern decorative look, perfect to complement and enhance any space
- The metal shade allows for a comfortable visual experience, reducing glare and creating a softer, inviting environment

Versatile Applications

- Available in two different shapes, sizes and finishes, these decorative pendants are ideal for residential and commercial environments such as dining areas, cafés, reception spaces, hospitality settings and more
- Offered with a 10' adjustable cable and perfect for use in high ceiling applications

quick
ship

DECORATIVE PENDANT MOUNTING KIT ACCESSORIES¹

Order Code	Model Number	Diameter (in.)	Cable Length (in.)	Finish	Compatible Luminaire (not included)	Master Case Qty	UPC
Cone							
70664	16IN CONE 10FT SUSP KIT BLACK FOR CLCR9	15 3/4	120	Black	70674	2	069549036420
70665	16IN CONE 10FT SUSP KIT WHITE FOR CLCR9	15 3/4	120	White	70674	2	069549036437
70668	19IN CONE 10FT SUSP KIT BLACK FOR CLCR12	19 1/8	120	Black	70675	2	069549036468
70669	19IN CONE 10FT SUSP KIT WHITE FOR CLCR12	19 1/8	120	White	70675	2	069549036475
Dome							
70666	15IN DOME 10FT SUSP KIT BLACK FOR CLCR9	14 5/8	120	Black	70674	2	069549036444
70667	15IN DOME 10FT SUSP KIT WHITE FOR CLCR9	14 5/8	120	White	70674	2	069549036451
70670	18IN DOME 10FT SUSP KIT BLACK FOR CLCR12	17 7/8	120	Black	70675	2	069549036482
70671	18IN DOME 10FT SUSP KIT WHITE FOR CLCR12	17 7/8	120	White	70675	2	069549036499

¹ Compatible luminaire is not included in mounting kit accessory and needs to be ordered separately (see compatible luminaire table).

COMPATIBLE LUMINAIRES (order separately)  *

Order Code	Model Number	Watts (W)	Lumen Output (lm) ^{2,3,4}	Efficacy (lm/W)	Color Temp. (K) ¹
70674 ³	CLCR9-R18W-A-5CWH	18	1 500	83	2 700/3 000/3 500/4 000/5 000
70675 ²	CLCR12-R24W-A-5CWH	24	2 115	88	2 700/3 000/3 500/4 000/5 000

* Only on 70674.

¹ Typical color temperature range: +/- 5 %.

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %.

³ Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %.

⁴ Lumen values are based on 3 000 K default programming. Please refer to the LUMEN SPECIFICATION TABLE for more details on other color temperatures.


Pair the CIRKA DECO luminaire with the pendant mounting kit accessory of your choice for a decorative look that fits any space.




Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

DIMENSIONS AND WEIGHTS


16" Cone




19" Cone



15" Dome



18" Dome



	Cone	Dome	
16"	16"	15"	18"
Net weight (lbs)	4.02	4.25	3.23

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.