

Tmax XT ranges

XT1 Accessories



Direct rotary handle



Extended rotary handle



IP54

Rotary handle operating mechanisms

Rotary handle operating mechanism

Type	Part number
RHD Standard Direct Handle	KXTRHDSTFP
RHD Emergency Direct Handle	KXTRHDEMFP
RHE Standard Extended Handle	KXTRHESTFP
RHE Emergency Extended Handle	KXTRHEEMFP
RHE Standard Extended Handle with Padlock	KXTRHESTFPPLK
RHE Emergency Extended Handle with Padlock	KXTRHEEMFPPLK
RHS-L Standard Left Side Handle	KXTRHSLSTFP
RHS-L Emergency Left Side Handle	KXTRHSLSEMFP
RHS-R Standard Right Side Handle	KXTRHRSRSTFP
RHS-R Emergency Right Side Handle	KXTRHRSREMFP
Extended handle spare parts	
RHE_B Base for Extended Handle	KXTRHEBFP
RHE_B Base for Extended Handle with Padlock ⁽¹⁾	KXTRHEBFPPLK
RHE_S 500mm Shaft	KXTARHES500
RHE_H Standard Extended Handle	KXTARHEHST
RHE_H Emergency Extended Handle	KXTARHEHEM
LH Standard Large Handle, NEMA 1	KXTALHNDLST
LH Emergency Large Handle, NEMA 1	KXTALHNDLEM
Standard Pistol Handle with reset function, 65mm, NEMA 3R,12	OHB65J10B
Emergency Pistol Handle with reset function, 65mm, NEMA 3R,12	OHY65J10B
Standard Pistol Handle with reset function, 65mm, NEMA 4,4X	OHB65L10B
Emergency Pistol Handle with reset function, 65mm, NEMA 4, 4X	OHY65L10B
Standard Pistol Handle with reset function, 125mm, NEMA 3R,12	OHB125J10B
Emergency Pistol Handle with reset function, 125mm, NEMA 3R,12	OHY125J10B
Standard Pistol Handle with reset function, 125mm, NEMA 4,4X	OHB125L10B
Emergency Pistol Handle with reset function, 125mm, NEMA 4, 4X	OHY125L10B
148mm Pistol Handle Shaft	OXPT10X148
225mm Pistol Handle Shaft	OXPT10X225
500mm Pistol Handle Shaft	OXPT10X500

IP54 protection for transmitted rotary handle⁽¹⁾

Type	Part number
IP54 protection for transmitted handle -RHE	KXTAERHEIP54

⁽¹⁾IEC rated only.

Flange handle

Type	Part number
Flange Handle + Mechanism + 4ft Cable (NEMA 1, 3R, 12, 4)	KXTN12FLHDL4
Flange Handle + Mechanism + 6ft Cable (NEMA 1, 3R, 12, 4)	KXTN12FLHDL6
Flange Handle + Mechanism + 10ft Cable (NEMA 1, 3R, 12, 4)	KXTN12FLHDL10
Flange Handle + Mechanism + 4ft Cable (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXTN4FLHDL4
Flange Handle + Mechanism + 6ft Cable (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXTN4FLHDL6
Flange Handle + Mechanism + 10ft Cable (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXTN4FLHDL10
Flange Handle Spare Parts	
Flange Handle only (NEMA 1, 3R, 12, 4)	KXTAN12FLHDL
Flange Handle only (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXTAN4FLHDL
Flange Handle Hardware	KXTAFLHDLHW
Flange Mounting Hardware	KXTBFLMTHW

⁽¹⁾Consult ABB for availability.