



Color: green/black



Connection Data

| | |
|-------------------------|--|
| Strip length | 3 ... 21 mm / 0.12 ... 0.83 inches |
| Solid conductor | 0.03 ... 16 mm ² / 32 ... 5 AWG |
| Fine-stranded conductor | 0.03 ... 16 mm ² / 32 ... 5 AWG |
| Stranded conductor | 0.03 ... 16 mm ² / 32 ... 5 AWG |

Mechanical data

| | |
|--|-----|
| Replaceable blade | Yes |
| Cutting function | Yes |
| Automatic conductor cross-section adjustment | Yes |
| Partial stripping function | Yes |

Material data

| | |
|--------------------|---------------------------|
| Color | green/black |
| Fire load | 0 MJ |
| Weight | 195 g |
| Conductor material | For copper / for aluminum |

Commercial data

| | |
|-----------------------|---------------|
| PU (SPU) | 1 pcs |
| Packaging type | Box |
| Country of origin | DE |
| GTIN | 4066966861747 |
| Customs tariff number | 82032000000 |

Product Classification

| | |
|-----------|----------------------|
| UNSPSC | 27112116 |
| ETIM 9.0 | EC002109 |
| ETIM 10.0 | EC002109 |
| ECCN | NO US CLASSIFICATION |

Environmental Product Compliance

| | |
|------------------------|-------------------------|
| RoHS Compliance Status | Compliant, No Exemption |
|------------------------|-------------------------|

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 206-1125



Documentation

Operating Instructions

| | | |
|---|------------------|--|
| Bedienungsanleitung 206-1125 Quickstrip Vario 2023 | pdf 926.95 KB | |
| Operating instructions 206-1125 Quickstrip Vario EN | pdf 925.13 KB | |

1 Compatible Products

1.1 Optional Accessories

1.1.1 Tool

1.1.1.1 Stripping tool



Item No.: 206-1128
Blade set; Oval blade, 10 mm² ... 16 mm²;
for 206-1125



Item No.: 206-1126
Blade set; Standard, 0.03 mm² ... 16 mm²;
for 206-1125



Item No.: 206-1127
Blade set; V-blade, 0.14 mm² ... 4 mm²;
for 206-1125



Item No.: 206-1131
Spare cut protector; for 206-1125



Item No.: 206-1132
Spare gripping jaws; for 206-1125



Item No.: 206-1129
Spare strip length stop; for 206-1125

Installation Notes



Cutting a conductor.



Partially stripping a conductor.