


**RT2W**




**RT230W**

## Automated lighting and fan control for convenience and energy savings


### RT2, RT230

These digital timer switches automatically turn off a connected lighting or fan load when the user-selected time expires. With four preset buttons – and timeframes up to 30 minutes (RT230) or 60 minutes (RT2) – users can rest assured lighting and power in low traffic areas won't be left on unintentionally. Adjustable time delays can be set for 5/10/15/30 minutes with RT230, or 10/20/40/60 minutes with the RT2. One minute before each time delay transition, the active button LED will flash, providing the end user with a visual countdown. As a part of the radiant® Collection, this timer can easily coordinate with matching switches, dimmers and outlets in the same collection.

### Features & Benefits




**Flying wire leads** for simple installation with green ground screw termination



**White LED locator light** glows when device is off for easy location in the dark

**Four-button preset timer switch**


**Manual ON/OFF control with paddle**



- **Works with a variety of light bulbs or fixtures including:** LED, CFL, ELV, MLV, Incandescent, Fluorescent, E-Ballast, and small motor loads
- **Automates control** of lights or small motor loads for energy savings and convenience
- **Adjustable time delay:**  
 RT2 – 10, 20, 40, 60 minutes  
 RT230 – 5, 10, 15, 30 minutes

- **Ideal for use with** bathroom fans, exhaust fans, closets, pantries, garages, attics, laundry rooms and more
- **Replace any basic switch** in 15 minutes or less (single-pole only)
- **Matching appearance** with other radiant® collection devices

### 3rd Party Compliance



## Technical Information

### Performance

Electrical	RT2	RT230
Supply Voltage	120VAC, 60Hz	120/277VAC, 60Hz
Output Voltage	120VAC, 60Hz	120/277VAC, 60Hz
Maximum Rated Load	800VA, 1/6HP	800VA (120V) /1800VA (277V), 1/4HP
Installation	Single Pole	
Neutral Required	Yes	

### Mechanical


Wire Termination	#16 AWG Flying Wire Leads, Ground Screw	
Unit Weight	0.23 lbs	
Wall Plate Size	NEMA 26-Opening	
Depth into Wall Box	1.19"	

### Environmental


Operating Conditions	0°C -55°C; 0-95% RH, non-condensing	
Flammability	UL94 V2	
Application	Indoor Use Only	
RoHS Compliant	Yes	
Prop65 Warning	No	
Country of Origin	China	

### Material Specs

Face/Enclosure	Polycarbonate	
Mounting Strap	Black Anodized Aluminum	



**RT230W**  
**Depth (Into Wallbox) = 1.19"**



## radiant® 4-Button Countdown Timers Ordering Information

Catalog No.	Description	Voltage	Load Rating	Color	UPC
RT2W	4-Button Timer Switch, 60-min	120VAC, 60Hz	All Lighting: 0-800VA Fan Motor: 1/6HP	White	78500703437
RT2LA				Light Almond	78500703436
RT2I				Ivory	78500703440
RT2BK				Black	78500703435
RT2NICCV4				Nickel	78500715838
RT2DBCCV4				Dark Bronze	78500715837

RT230W	4-Button Timer Switch, 30-min	120/277VAC, 60Hz	All Lighting: 0-800VA @ 120VAC 0-1800VA @ 277VAC Fan Motor: 1/4HP	White	78500705234
RT230LA				Light Almond	78500705233
RT230I				Ivory	78500705232
RT230BK				Black	78500705231

## Guide Specifications

Four-Button Digital Timer: radiant® Catalog No. RT2[I][W][LA][BK][DB][NI]CCV4; rated 800VA at 120VAC, 60Hz for LED, CFL, incandescent, fluorescent, E-ballast, MLV, ELV, or 1/6HP motors at 120VAC, 60Hz; #16 AWG wire leads; 10-60 minutes time delay; manual ON; visual countdown time remaining out warning; impact resistant thermoplastic enclosure; [ivory][white][light almond][black] color; five (5) year warranty.

Four-Button Digital Timer: radiant® Catalog No. RT230[I][W][LA][BK]; rated 800VA at 120VAC and 1800VA at 277VAC, 60Hz for LED, CFL, incandescent, fluorescent, E-ballast, MLV, ELV, or 1/4HP motors at 120VAC, 60Hz; #16 AWG wire leads; 5-30 minutes time delay; manual ON; visual countdown time remaining out warning; impact resistant thermoplastic enclosure; [ivory][white][light almond][black] color; five (5) year warranty.

## Vertical Markets

- Residential
- Light Commercial
- Multiple Dwelling
- Restaurants
- Hospitality/Lodging
- Office/Education

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
 60 Woodlawn Street  
 West Hartford, CT 06110  
 1-877-295-3472  
[www.legrand.us](http://www.legrand.us)

**Canada**  
 1-844-977-3783  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

