# **Covers**

#### **Cover Selection Guide**

### **Tray Covers**

Tray covers are available for all widths of tray. They should be installed where falling objects may damage cables or where vertical tray run is accessible by pedestrian or vehicular traffic.

#### **Straight Covers**

These covers provide maximum mechanical protection for cables with limited heat build up. Flanged covers have 1/2 in. flange.



Note: Cover mounting hardware must be ordered separately.

### **Straight Cover Number Selection**



(ALT) F 03 SFC 3								
Material Prefix	Series Prefix	Туре	Width	Bottom Style	Length			
AL • Aluminum SP • Pregalvanized SH • Hot-dipped galvanized SS • 316 Stainless steel	T • Cable channel	Accessory i.e.: Straight cover	01 • (1.5 in.) 03 • (3 in.) 04 • (4 in.) 06 • (6 in.)	SFC • Solid flanged covers	3 • (10 ft.)			

<sup>\*</sup>Hot-dipped galvanized covers only available in 1500 mm lengths

Quantity of Standard Cover Clamps Required		
Straight section (10 ft.)	6 pcs.	
Note: When using the heavy-duty cover clamps, only half the quantity of pieces are required.		





## Covers

### **Tray Covers**

Tray covers are available for all widths of tray. They should be installed where falling objects may damage cables or where vertical tray run is accessible by pedestrian or vehicular traffic.

### **Fitting Covers**

Fitting covers are available to complete your cable channel layout. All fitting covers are flanged.



Note: Cover mounting hardware must be ordered separately.

### **Fittings Number Selection**



(ALT) F 06 HBC 45 12								
Material Prefix	Series Prefix	Туре	Width	Type Cover	Degree*	Radius		
AL • Aluminum SP • Pregalvanized SH • Hot-dipped galvanized SS • 316 Stainless steel	T • Cable channel	F ● Fitting cover	01 • (1.5 in.) 03 • (3 in.) 04 • (4 in.) 06 • (6 in.)	HBC • Horizontal bend HTC • Horizontal tee HXC • Horizontal cross VOC • Vertical outside bend VIC • Vertical inside bend	30 • 30° 45 • 45° 60 • 60° 90 • 90°	12 • 12 in. 24 • 24 in. 0 • Zero† radius  †Contact your Regional Sales Office for availability		

<sup>\*</sup>Required for HB, VI & VO only.

Quantity of Standard Cover Clamps Required		
Horizontal and vertical bends Tees Crosses	4 pcs. 6 pcs. 8 pcs.	
Note: When using the heavy-duty cover clamps, only half the quantity of pieces are required.		