


LED Large Flood S3

STANDARD's Large Flood S3 luminaires provide a wide beam with a 7H x 7V distribution. Ideal for multiple applications such as signs, large building facades and general area lighting when a shorter setback is needed.



Order code	Description	Watts	Volts	Colour temp.	CRI	Life L70	Lumen output	Finish	NEMA type	Traditional equivalent (W)		Case qty
		(W)	(VAC)	(K)		(hrs)	(lm)			MH	HPS	(master)
Yoke												
66932	FL/S3/100-277/300W/40K/YK/BZ/STD	300	100-277	4 000	70	50 000	39 454	Bronze	7H x 7V	1000	1000	1
66936	FL/S3/277-480/300W/40K/YK/BZ/STD	300	277-480	4 000	70	50 000	41 454	Bronze	7H x 7V	1000	1000	1
66940	FL/S3/100-277/400W/40K/YK/BZ/STD	400	100-277	4 000	70	50 000	50 807	Bronze	7H x 7V	1000	1000	1
66944	FL/S3/277-480/400W/40K/YK/BZ/STD	400	277-480	4 000	70	50 000	50 859	Bronze	7H x 7V	1000	1000	1




Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products,
please visit www.standardpro.com



LED Area and Roadway S3

STANDARD's Area and Roadway S3 luminaires are perfectly suited to light up roadways, parking lots and general areas with their type III light distribution. Their new design allows changing mounting brackets to fit into multiple applications and an offering of accessories also add to the possibilities of mounting types.

- Slipfitter mount included with luminaire
- Optional straight arm mount accessory



Order code	Description	Watts (W)	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Finish	Distribution type	Traditionnal equivalent (W)		Case qty (master)
										MH	HPS	
Slip Fitter												
66934 ¹	ARL/S3/100-277/300W/40K/III/SF/BZ/STD	300	100-277	4 000	70	39 454	40 500	Bronze	Type III	750	750	1
66938 ¹	ARL/S3/277-480/300W/40K/III/SF/BZ/STD	300	277-480	4 000	70	41 454	40 500	Bronze	Type III	750	750	1
66942 ¹	ARL/S3/100-277/400W/40K/III/SF/BZ/STD	400	100-277	4 000	70	50 807	52 000	Bronze	Type III	1000	1000	1
66946 ¹	ARL/S3/277-480/400W/40K/III/SF/BZ/STD	400	277-480	4 000	70	50 859	52 000	Bronze	Type III	1000	1000	1
Optional Straight Arm Mounting												
67055	FL/S3/ACC/MA/STD	-	-	-	-	-	-	Bronze	-	-	-	6



Accessories

Order code	Description	Type	Finish	Compatible with
66155	LFL/L/S2/ACC/SF/SQR POLE MOUNT/STD	Slip fitter to square pole mount Straight arm to round pole mount 4", 5" & 6"	Bronze	66934, 66938, 66942, 66946
66702	LFL/L/S2/ACC/MA/RND POLE MOUNT/STD		Bronze	66934, 66938, 66942, 66946



Lumen values are derived from photometric testing
For a complete list of compatible dimmers and DLC qualified products,
please visit www.standardpro.com
¹ Use a post with a diameter of 2 3/8"