

ACCESSORIES


GUARDS

These die cast guards have inside threading and a set screw to lock the guard in place.



CAT #	DESCRIPTION
GD100CGS	Cast Guard 100 Series
GD200CGS	Cast Guard 200 Series

These chrome plated guards have a nut and bolt to secure the guard to the fixture. Please note these guards will fit on fixtures that have polycarbonate or plastic globes.



CAT #	DESCRIPTION
GD100CL	Wire Guard 100 Series
GD200CL	Wire Guard 200 Series

REFLECTORS

Highly reflective white powder coat paint finish inside and out over a heavy gauge metal base. Reflector is attached to globe holder ring by four screws so that it and the guard are removed during relamping.



CAT #	DESCRIPTION
VR100A	30° Angle Dome 100 Series
VR200A	30° Angle Dome 200 Series
VR100-16	16" Standard Dome 100 Series
VR200-16	16" Standard Dome 200 Series

GLOBES

Various globe options are available to fit our standard weatherproof fixtures in both the 100 and 200 series. Below are the polycarbonate and glass globes available.

For coloured glass our RGL series is superior in that it retains its' colour longer than painted glass. This is achieved by having the colour impregnated into the glass as it is being made. Available colours are amber, blue, green and red.

GLOBES 100 Series

	CAT #	DESC.	MAX. WATT (Inc.)
	GL100	Clear Glass	100
	GL100HR	Heat Resistant Glass	100
	GL100CL-RIB	Clear Prismatic Glass	100
	GL100SB	Frosted Glass	100
	GL100CPR	Prismatic Polycarbonate	75
	RGL100A	Amber Glass	100
	RGL100B	Blue Glass	100
	RGL100G	Green Glass	100
	RGL100R	Red Glass	100
		GL100WB	White Glass
GL100PG		Clear Polycarbonate	75
GL100PGO		White Polycarbonate	75
GL100PGA		Amber Polycarbonate	75
GL100PGB		Blue Polycarbonate	75
GL100PGG		Green Polycarbonate	75
	GL100PGR	Red Polycarbonate	75
	GL100BO	White Ball Glass	100
	GL100PGB0	White Ball Polycarbonate	75
	GLB100CP	Clear Polycarbonate Ball	75
	GL100LWP	Long White Prismatic	75
	GL100LPR	Long Clear Prismatic	75
	GL100PRS	6" Long Clear Prismatic	75

200 Series

	CAT #	DESC.	MAX. WATT (Inc.)	
	GL200	Clear Glass	200	
	GL200HR	Heat Resistant Glass	200	
	GL200CL-RIB	Clear Prismatic Glass	200	
	GL200SB	Frosted Glass	200	
	RGL200A	Amber Glass	200	
	RGL200B	Blue Glass	200	
	RGL200G	Green Glass	200	
	RGL200R	Red Glass	200	
		GL200PG	Clear Polycarbonate	150
		GL200PGO	White	150

W
E
A
T
H
E
R
P
R
O
O
F

