

Product family features

- Can be used in conjunction with the following dimmer(s), switch(es), sensor(s), and accessories: Maestro®, Maestro IR®, Maestro Wireless®, Caséta® Wireless, Pico® wireless, Diva®, Skylark Contour® and Skylark® controls, and Claro® and Satin Colors® accessories
- All Lutron wallplates are screwless, seamless, and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in Designer style opening
- Blank inserts available for Gloss (DV-BI-) and Satin Colors (SC-BI-)


Ganging and derating

- Designer wallplates use standard ganging
- Requires fins to be removed from dimmers for proper spacing (“Fins Broken” ganging)
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables

Available finishes

Use **BOLD** color code in model number (Example: SC-1-**PL**)

Gloss finishes



WH
White

LA
Light Almond

AL
Almond


IV
Ivory

GR
Gray

BR
Brown

BL
Black

Satin Colors® finishes



SW
Snow

LS
Limestone


BI
Biscuit

ES
Eggshell

PD
Palladium

TP
Taupe

ST
Stone



BG
Bluestone

PL
Plum

SG
Sea Glass

TQ
Turquoise

GS
Goldstone

DS
Desert Stone

GB
Greenbriar

Metal finishes*



MS
Mocha Stone

TC
Terracotta

SI
Sienna

HT
Hot


MR
Merlot

MN
Midnight

SS
Stainless Steel

*Stainless Steel finish wallplates include black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Wallplates for Maestro®, Maestro IR®, Maestro Wireless®, Caséta® Wireless, Pico® wireless, Diva®, Skylark Contour® and Skylark® controls, and Claro® and Satin Colors® accessories



1-gang*

CW-1-**XX**¹
SC-1-**XX**²


W: 2.94 in (75 mm); H: 4.69 in (119 mm)
P: .30 in (7.6 mm)



4-gang*

CW-4-**XX**¹
SC-4-**XX**²

W: 8.37 in (213 mm); H: 4.69 in (119 mm);
P: .30 in (7.6 mm)



2-gang*

CW-2-**XX**¹
SC-2-**XX**²

W: 4.75 in (121 mm); H: 4.69 in (119 mm);
P: .30 in (7.6 mm)



5-gang*

CW-5-**XX**¹
SC-5-**XX**²

W: 10.18 in (259 mm); H: 4.69 in (119 mm);
P: .30 in (7.6 mm)



3-gang*

CW-3-**XX**¹
SC-3-**XX**²

W: 6.56 in (167 mm); H: 4.69 in (119 mm);
P: .30 in (7.6 mm)


XX¹: Gloss and metal color codes
XX²: Satin Colors® codes

Multi-gang dimmer installations may require derating.


*Stainless Steel finish wallplates include black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Designer | Claro® and Satin Colors® Wallplates & Accessories


Wallplates




1-gang
CW-1-
SC-1-




5-gang
CW-5-
SC-5-




2-gang
CW-2-
SC-2-



6-gang
CW-6-
SC-6-



3-gang
CW-3-
SC-3-



4-gang
CW-4-
SC-4-