

Modular Enclosures

Replacement parts

Roof plate | CCR


Description: Standard roof plate to cover the top of the floor standing combinable range.

Material: 1.5 mm steel plate.

Finish: RAL7035 structured powder coating.

Pack quantity: 1 piece without mounting accessories.

Mounting requirement: Standard roof plate for separate delivery. For mounting, add CCRKS mounting kit.



W	D	Catalog No.
400	400	CCR044R5
500	500	CCR055R5
600	400	CCR064R5
600	500	CCR065R5
600	600	CCR066R5
600	800	CCR068R5
800	400	CCR084R5
800	500	CCR085R5
800	600	CCR086R5
800	800	CCR088R5
800	1000	CCR0810R5
1000	400	CCR104R5
1000	500	CCR105R5
1000	600	CCR106R5
1000	800	CCR108R5
1200	400	CCR124R5
1200	500	CCR125R5
1200	600	CCR126R5
1200	800	CCR128R5
1400	400	CCR144R5
1600	400	CCR164R5
1600	500	CCR165R5
1600	600	CCR166R5
1800	500	CCR185R5
1800	600	CCR186R5
1800	800	CCR188R5

All measurements are in mm.

Modular Enclosures

Replacement parts

Rear panel | CRP

Description: Can be replaced by a plain or transparent door.

Material: 1.5 mm steel plate.

Delivery: 1 rear panel.

H	W	Catalog No.
1100	600	CRP1106R5
1200	600	CRP1206R5
1200	800	CRP1208R5
1200	1200	CRP1212R5
1400	600	CRP1406R5
1400	800	CRP1408R5
1400	1200	CRP1412R5
1600	600	CRP1606R5
1600	800	CRP1608R5
1600	1000	CRP1610R5
1600	1200	CRP1612R5
1800	600	CRP1806R5
1800	800	CRP1808R5
1800	1000	CRP1810R5
1800	1200	CRP1812R5
1800	1600	CRP1816R5
1800	1800	CRP1818R5
2000	400	CRP2004R5
2000	600	CRP2006R5
2000	800	CRP2008R5
2000	1000	CRP2010R5
2000	1200	CRP2012R5
2000	1600	CRP2016R5
2000	1800	CRP2018R5
2200	600	CRP2206R5
2200	800	CRP2208R5
2200	1000	CRP2210R5

All measurements are in mm.



Roof mounting kit | CCRK

Description: Standard mounting accessories for the CCR and CRG roof plates.

Delivery: 4 pieces M12x20, 4 pieces M6x12 and 4 pieces M12 plastic washers.

Catalog No.
CCRK08



Modular Enclosures

Replacement parts

Rear panel mounting kit | CRPK

Description: Standard mounting accessories for the back panel.

Delivery: 8 rear panel brackets, 16 pieces extrude-tite M6x12. EPDM sealing part.

W	Catalog No.
400	CRPK04
500	CRPK05
600	CRPK06
800	CRPK08
1200	CRPK12*
1600	CRPK16

*Use CRPK12 for 1000 Wide Enclosures.

All measurements are in mm.



Door plastic support | DPSL

Description: Helps to center the door in case of uneven floor, easier closing and positioning of a heavily equipped door (cooling units, etc.). Mounted directly to the door frame on the bottom and top of the door. Highly recommended when fitting loads from 30 kg on door.

Delivery: 2 plastic supports with mounting accessories.

Catalog No.
DPSL01



Mounting plate brackets | MPA

Description: To fix mounting plates to the furthest position in the rear of the enclosure, including adjustment brackets for depth adjustment in steps of 25 mm. Brackets are needed when an extra mounting plate is required or when the enclosure is ordered without mounting plate (PE).

Material: 3 mm zinc plated steel.

Delivery: 2 top brackets, 2 bottom sliding brackets and 2 adjustment brackets with mounting accessories.

Catalog No.
MPA06

