

Wire Marker Books

Markers that withstand oil, water and humidity!

Vinyl Cloth, Standard Books

- Choose the numbers or letters you need
- Wide selection of sizes and legends
- Size 3 in. x 5 in. (76 mm x 146 mm)
- Material: vinyl cloth
- Cover keeps markers clean
- Books are 3 in. x 5-1/2 in. pocket size
- 10 pages per book

Easy to Use!

Pocket pack wire marker books are easy to carry and easy to use. The material is an all-purpose vinyl coated cloth tape exclusively designed to resist abrasion, oil, water and dirt.

From Thomas & Betts you get the one-piece wire marker and terminal marker. A slight die-cut enables you to easily remove the terminal.



Cat. No.	Number of Markers and Legends
WM-0 thru 9	40 markers each: 0 thru 9; 10 markers each: T1, T2, T3, L1, L2, L3, WM-0 thru -9
WM-0-9M	46 markers each page; full page of 1, full page of 2, etc.
WM-0-45	10 markers each: 0 thru 45
WM-46-90	10 markers each: 46 thru 90
WM-A-Z	10 markers each: A thru Z, +, -, and 0 thru 15
WM-123	150 markers each: 1, 2, 3
WM-ABC	150 markers each: A, B, C
WM-A-33	10 markers each: 1 thru 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3
WM-A-90	6 markers each: 0 thru 15; 4 markers each: 1
WM-0 thru WM-9	2 markers each; 6 thru 90, A thru Z 460 markers each of any number 0 thru 9
WM-A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T, or X	460 markers each of any letter: -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or -X
WM-GRD	120 markers 7/16 in. X 2-1/2 in. or 240 markers 7/16 in. x 1-1/4 in. "GRD" legend
WMLC-1	24 legends, 2 legends each per page, 480 markers per book for house wiring and circuit breakers; 5/8 in. x 13/32 in. (16 mm x 10 mm)

Cat. No.	Number of Markers and Legends
WM-T3	10 pages T1, T2, T3; 140 markers ea.; Total 420
WM-L3	10 pages L1, L2, L3; 140 markers ea.; Total 420
WM-9T	3 pages 1, 2, 3; 42 markers ea.; 3 pages A, B, C; 42 markers ea.; 2 pages T1, T2, T3; 28 markers ea.; 2 pages L1, L2, L3; 28 markers ea.; Total 140
WM-1-30	10 Pages 1-30; 14 markers ea.; Total 140
WM-12	8-2/3 Pages A-Z, 14 markers ea.; Blank Write-Ons 1 Page, 22 markers; Plus & Minus 1/3 Page, 7 markers ea.; Total 393
WM-13	Plus & Minus, AC, DC, 1 Page ea., 46 markers ea.; Pos. Neg. Gnd. 1 Page ea., 28 markers ea.; Spare, Neut. 1 Page ea., 22 markers ea.; Blank Write-Ons 1 Page ea., 22 markers ea.; Total 256
WM-0-90	5 pages, 0-45; 5 markers ea.; 5 pages, 46-90; 5 markers ea.; Total 455

Wire Marker Books

A handy solution for your identification needs!




Compact Wire Marker Books

- Compact books are easier to carry
- Bold letters/numbers, easy to apply and read
- Convenient alphanumeric and load center legends
- E-Z-Snap feature removes the entire sheet more easily from the booklet
- Vinyl coated cloth

Cat. No.	Number of Markers and Legends
WCMB-0-9	128 markers 0-9, ABC, +-/; marker size 1/4 in. x 1-1/2 in.
WCMB-LC	176 markers Load-center Labels; marker size 1-1/32 in. x 3/4 in.


Identify and protect all in one!



Vinyl Self-Laminating Books

- Convenient alphanumeric legends
- Lamination keeps markers protected


Cat. No.	Number of Markers and Legends
WMSL 1-33, A-G	400 markers: 1/4 in. x 1-1/4 in.— printed area 5/8 in.; 10 markers each: 1 thru 33 and A thru G
WMSL-0-9	40 markers each 0 thru 9; 10 markers each: T1, T2, T3, L1, L2, L3
WMSL-0-45	10 markers each 0 thru 45
WMSL-46-90	10 markers each 46 thru 90
WMSL-A-Z	10 markers each: A thru Z; +, -, and 0 thru 15
WMSL-A-90	6 markers each: 0 thru 15; 4 markers each 16 thru 90; 2 markers each A thru Z



Vinyl Self-Laminating, Blank Write-on Books

- Choose from a variety of marking area sizes
- Clear area covers print legend for extra protection
- Lamination keeps markers protected

Cat. No.	Number of Markers and Legends
WM-BW3	30 markers 1 in. x 4-7/8 in. blank write-on, self-laminating markers; marking area: 1 in. x 1 in.
WM-BW5	60 markers 1 in. x 2-3/4 in. blank write-on, self-laminating markers; marking area: 1 in. x 3/4 in.
WM-BW12	200 markers 1/2 in. x 1-1/4 in. blank write-on, self-laminating markers; marking area: 1/2 in. x 5/8 in.
WM-BW14	400 markers 1/4 in. x 1-1/4 in. blank write-on, self-laminating markers; marking area: 1/4 in. x 5/8 in.
WM-BW34	140 markers 3/4 in. x 1-1/4 in. blank write-on, self-laminating markers; marking area: 3/4 in. x 5/8 in.



Vinyl Self-Laminating, Standard Laminator Book

- Protect labels or apply over non-sticking markers
- 50, 3-1/2 in. x 5 in. clear cable laminators

Cat. No.	Number of Markers and Legends
WM-LAM	50, 3-1/2 in. x 5 in. clear cable laminators