


## Industrial grade straight blade receptacles


### Product description

2-pole, 3-wire grounding  
 15A, 125V/AC;  
 20A, 125V/AC  
 NEMA 5-15R, 5-20R




5-15R


5-20R




AH5362



AH5262\_M




6362



AHIG5362

### Premium industrial grade receptacles



Rating		NEMA	Description	Color suffix	Catalog no.	
A	V/AC					
15	125	5-15R	Premium duplex receptacle, back & side wire	B, BK, GY, RD, V, W	<input type="checkbox"/> AH5262__	• • • •
			Premium single receptacle, back & side wire	B, GY, RD, V, W	<input type="checkbox"/> 5261__	• • • •
20	125	5-20R	Premium duplex receptacle, back & side wire	B, BK, GY, LA, RD, V, W	<input type="checkbox"/> AH5362__	• • • •
			Premium single receptacle, back & side wire	B, BK, GY, RD, V, W	<input type="checkbox"/> 5361__	• • • •

### Premium decorator industrial grade receptacles



Rating		NEMA	Description	Color suffix	Catalog no.	
A	V/AC					
15	125	5-15R	Premium decorator duplex receptacle, back & side wire	GY, RD, V, W	<input type="checkbox"/> 6262__	• • • •
20	125	5-20R	Premium decorator duplex receptacle, back & side wire	BK, GY, RD, V, W	<input type="checkbox"/> 6362__	• • • •

### Isolated ground premium industrial grade receptacles



Rating		NEMA	Description	Color suffix	Catalog no.	
A	V/AC					
15	125	5-15R	Premium IG duplex receptacle, back & side wire	GY, RD, RN, V, W	<input type="checkbox"/> AHIG5262__	• • • •
			Premium IG single receptacle, back & side wire	RN	<input type="checkbox"/> IG5261RN	• • • •
20	125	5-20R	Premium IG duplex receptacle, back & side wire	BK, GY, RD, RN, V, W	<input type="checkbox"/> AHIG5362__	• • • •
			Premium IG single receptacle, back & side wire	RN, V	<input type="checkbox"/> IG5361__*	• • • •

\*Not Fed Spec

### Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)



**Specification information:** Premium industrial receptacles: A-29, ArrowLink premium industrial receptacles: A-36, Premium decorator industrial receptacles: A-29, Isolated ground premium industrial receptacles: A-34, ArrowLink isolated ground premium industrial receptacles: A-31, A-36

**Compliances, specifications and availability are subject to change without notice.**

ArrowLink option available. Add "M" suffix to standard catalog number (example AH8300W, AH8300WM). For ordering information on ArrowLink & ArrowLink SPD connectors, see Page A-5

Build-to-spec customizable devices - Page A-6

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32