



SIGN UP / LOG IN



48-89-9115

Step Drill Bit, 7/8" Single Hole

★★★★★ (0) Write a review

Our line of step drill bits far surpasses the competition. With our single cutting edge design, you will have more control and a cleaner finish. Made of high speed steel, these new step drill bits are durable and designed to drill through most metals. The black oxide finish prevents corrosion and has great capacity to work with drilling lubricants. The new speed start tip prevents bit walking and allows faster penetration. With laser etched markings you will always know your hole sizes...no guess work! Finally, the 3-flat shank prevents slipping in the chuck.

Close

INCLUDES:

(1) Step Drill Bit, 7/8" Single Hole (48-89-9115) (/Products-Repository/North-America/Accessories/Drilling/Metal-Drilling/Step-Drill-Bits/Step-Drill-Bits/48-89-9115)

This product is no longer available. Feel free to contact us for suggestions of other products that may fit your needs. Contact Us (/contact)

KEY FEATURES

Single Cutting Edge provides true round holes every time

High Speed Steel Make-up is ideal for cutting into stainless steel, aluminum, brass, copper, plastic and more

Black Oxide Finish resists corrosion for longer life

SPECIFICATIONS

REVIEWS

Speed Start Tip starts fast and reduces the risk of bit walking

Laser Etched Markings for fast, easy hole size identification

3-Flat Shank prevents bit from slipping in the chuck

PRODUCT SPECIFICATIONS

Increments	NA
Coating	Black Oxide
Shank	3/8"
Application	Metal Plastic
Size	7/8"
Number of Steps	1

REVIEWS



Be the first to review this product

You Might Also Like



M18 FUEL™ 1/2" Hammer Drill/Driver Kit

(/Products/Power-Tools/Drilling/Hammer-Drills/2604-22CT)



M12 FUEL™ 1/2" Hammer Drill/Driver Kit

(/Products/Power-Tools/Drilling/Hammer-Drills/2404-22)



SIGN ME UP!

Be the first to know about special offers, new product launches and events.

Email Address*

Trade*
Select a Trade

Zip Code*

Subscribe

(https://www.milwaukeetool.com/Products/Power-Tools/Fastening/Impact-Wrenches/2766-20) 443430746518713

PRODUCTS

- [Power Tools \(/Products/Power-Tools\)](#)
- [Lighting \(/Products/Lighting\)](#)
- [Hand Tools \(/Products/Hand-Tools\)](#)
- [Storage \(/Products/Storage-Solutions\)](#)
- [Work Gear \(/Products/Work-Gear\)](#)
- [Instruments \(/Products/Instruments\)](#)
- [Accessories \(/Products/Accessories\)](#)

ABOUT US

- [Milwaukee Story \(/Company/Milwaukee-Story\)](#)
- [Press Releases \(/News/Press-Releases\)](#)
- [Milwaukee Swag \(https://www.milwaukeetoolswag.com\)](#)
- [Careers \(https://www.milwaukeetool.jobs/\)](#)
- [Contact Us \(/Contact\)](#)



US :: EN - Change Site / Language (/Country-Selector)



Where to Buy Milwaukee Products (/Buy-Now)

NEW PRODUCTS

M18 FUEL™ High Torque ½” Impact Wrench with Pin Detent - 2766-20 (/Products/Power-Tools/Fastening/Impact-Wrenches/2766-20)

M18 FUEL™ Drain Snake w/ CABLE DRIVE™ - 2772A-20 (/Products/Power-Tools/Drain-Cleaning/Sink-Machines/2772A-20)

M18™ RADIUS™ Site Light/Charger w/ ONE-KEY™ - 2150-20 (/Products/Lighting/Site-Lights/2150-20)

PACKOUT™ Rolling Tool Box - 48-22-8426 (/Products/Storage-Solutions/PACKOUT/PACKOUT-Tool-Boxes/48-22-8426)

SHOCKWAVE Linemans Impact Auger Bits (/Products/Accessories/Metal-Drilling/Wood-Boring-Bits/SHOCKWAVE Linemans Impact Auger Bits)

HOW CAN WE HELP?

- [Contact Us \(/Contact\)](#)
- [eService Repair \(/eService\)](#)
- [Find A Service Center \(/Support/Find-A-Service-Center\)](#)
- [Manuals and Downloads \(/Support/Manuals-and-Downloads\)](#)
- [Work At Milwaukee \(https://www.milwaukeetool.jobs/\)](#)

© 2018 by Milwaukee Tool. All rights reserved.

[Legal \(/Footer/Legal\)](#) | [Safety Notices \(/News/Safety-Notices\)](#) | [Privacy \(/Footer/Privacy\)](#) | [Contact Us \(/Contact\)](#)