

DB42



DB42 Single Mounting Kit



General Information

Extended Product Type	DB42
Product ID	1SAZ701902R0001
EAN	4013614407826
Catalog Description	DB42 Single Mounting Kit
Long Description	DB42 Single Mounting Kit for TF42

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85389099

Popular Downloads

Data Sheet, Technical Information	1SBC100173C0201
Instructions and Manuals	2CDC106025M6802
Dimension Diagram	1SAZ700410F0001

Dimensions

Product Net Width	108 mm
Product Net Height	50 mm
Product Net Depth / Length	102 mm
Product Net Weight	0.087 kg

Technical

Rated Operational Voltage	Main Circuit 690 V AC
Rated Operational Current (I_e)	40 A
Rated Operational Current AC-3 (I_e)	40 A
Rated Frequency (f)	Main Circuit 50 Hz Main Circuit 60 Hz
Rated Impulse Withstand Voltage (U_{imp})	Main Circuit 6 kV Auxiliary Circuit 6 kV
Rated Insulation Voltage (U_i)	690 V
Number of Poles	3

Degree of Protection	IP20
Pollution Degree	3
Connecting Capacity Main Circuit	Rigid 1x 0.75 ... 2.5 mm ² Flexible with Ferrule 1x 0.75 ... 10 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 10 mm ² Flexible 1x 0.75 ... 10 mm ²
Tightening Torque	Main Circuit 1.5 ... 2.7 N·m
Wire Stripping Length	Main Circuit 12 mm
Recommended Screw Driver	Pozidriv 2
Mounting Position	Position 1 to 5
Suitable For	TF42
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 508 CSA 22.2 No. 14

Environmental

Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 25g
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 3 ... 150 Hz
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Ampere Rating UL/CSA	40 A
Connecting Capacity Main Circuit UL/CSA	Stranded 1x 18 ... 6 AWG Flexible 1x 18 ... 6 AWG
Tightening Torque UL/CSA	Main Circuit 13 ... 22 in·lb

Certificates and Declarations (Document Number)

ABS Certificate	No Certificate Needed
cUL Certificate	cUL_E48139
Declaration of Conformity - CE	1SAD938509-0181 1SAD938502-0199
DNV Certificate	No Certificate Needed
GL Certificate	No Certificate Needed
GOST Certificate	1SAA941000-2704
Instructions and Manuals	2CDC106025M6802
LR Certificate	No Certificate Needed
RINA Certificate	No Certificate Needed
RMRS Certificate	No Certificate Needed
RoHS Information	1SAD938508-0181
UL Certificate	UL_E48139

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	108 mm
Package Level 1 Height	50 mm
Package Level 1 Depth / Length	102 mm

Package Level 1 Gross Weight	0.12 kg
Package Level 1 EAN	4013614407826
Package Level 2 Units	84 piece
Package Level 2 Width	405 mm
Package Level 2 Height	360 mm
Package Level 2 Depth / Length	380 mm
Package Level 2 Gross Weight	73.08 kg
Package Level 2 EAN	4013614480010

Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC002498 - Accessories for low-voltage switch technology
ETIM 6	EC002498 - Accessories for low-voltage switch technology
ETIM 7	EC002498 - Accessories for low-voltage switch technology
eClass	7.0 27379201

Categories

Low Voltage Products and Systems → Control Products → Contactors → Thermal Overload Relays Accessories

