



# TRAC-MASTER®

Mounting Accessories

## MONOPOINTS and SPECIAL MOUNTINGS

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

### PRODUCT DESCRIPTION

Special adapters permit the flexibility of mounting trac lights in various ways to meet special requirements.

### Line Voltage Monopoint Adapters

Example: T40N BL

| T40N<br>BL, SL, WH  | T40F<br>BL, SL, WH   | T41N<br>BL, SL, WH  | T42N<br>BL, WH   |
|---|--|---|--|
| <p><b>Monopoint Adapter</b></p> <p>Mounts directly to outlet box. Accepts one 120V Juno trac fixture.</p> | <p><b>Flush Monopoint Adapter</b></p> <p>Mounts directly to 4" outlet box only. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.</p> | <p><b>Duo-Point Adapter</b></p> <p>Mounts directly to an outlet box. Accepts two 120V Juno trac fixtures.</p> | <p><b>Weighted Base</b></p> <p>For portable use. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture.</p> |

| T45<br>BL, WH  | T46  | T57N<br>WH  |
|--|--|---|
| <p><b>Pin-Up/Monopoint Adapter</b></p> <p>Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.</p> | <p><b>Clamp/Monopoint Adapter</b></p> <p>Clamps to pipe or planking up to 2-1/2" thick. Accepts one 120V Juno trac fixture. Supplied with 8' three-wire cord and plug.</p> | <p><b>Monopoint Line Voltage Cover</b></p> <p>Attaches one 120V trac fixture directly to Juno's 6" recessed universal housings.</p> |

### Line Voltage Coil – Cord Clamp-Ons

Example: T132 WH

| T132<br>BL, WH   | T132 WA<br>BL, WH  | T133<br>BL, WH   | T133 WA<br>BL, WH   |
|--|--|--|---|
| <p><b>120V Monopoint with Trac Adapter</b></p> <p>120V Monopoint with trac adapter for electrical connection to Trac. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.</p> | <p><b>120V Monopoint with Trac Adapter</b></p> <p>Same as <b>T132</b> but accepts one 120V Juno Trac fixture with wide trac adapter.</p> | <p><b>120V Monopoint with Male Plug</b></p> <p>120V Monopoint with male plug (120V) attaches to receptacle. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.</p> | <p><b>120V Monopoint with Male Plug</b></p> <p>Same as <b>T133</b> but accepts one 120V Juno Trac fixture with wide trac adapter.</p> |
| <p>2' Coil Cord extends to 5'.<br/>1-3/4" Clamp opening.</p>   |  |  |   |

# TRAC-MASTER®

Mounting Accessories

## MONOPOINTS and SPECIAL MOUNTINGS

### Line Voltage Extension Wands

Examples: TEW 12IN BL, TEWS WH WA


| TEW  | TEW WA   | TEWS   | TEWS WA   |
|--|--|--|---|
| 12IN, 18IN, 24IN, 36IN, 48IN   | 12IN, 18IN, 24IN, 36IN, 48IN   |  |   |
| BL, SL, WH   | BL, SL, WH   | BL, SL, WH   | BL, SL, WH  |
| <p><b>Line Voltage Extension Wands</b></p> <p>For use with one or two circuit trac and line voltage monopoints. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.</p> | <p><b>Line Voltage Extension Wands</b></p> <p>Same as <b>TEW</b> but accepts one 120V Juno trac fixture with <u>wide</u> trac adapter.</p> | <p><b>24" Wand Slope Adapter</b></p> <p>Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.</p> | <p><b>24" Wand Slope Adapter</b></p> <p>Same as <b>TEWS</b> but accepts one 120V Juno trac fixture with <u>wide</u> trac adapter.</p> |



### Line Voltage Slope Ceiling Adapter

Examples: T95 BL, T95 WH WA

| T95  | T95 WA   |
|--|--|
| BL, BZ, SL, WH   | BL, BZ, SL, WH   |
| <p><b>Slope Ceiling Adapter</b></p> <p>Attaches to trac, permitting Trac-Master or Trac-Lites Trac fixtures with <u>standard size</u> trac adapter to be hung vertically from sloped ceiling. 90° maximum adjustable</p> | <p><b>Slope Ceiling Adapter</b></p> <p>Same as above but accepts one 120V Juno Trac fixture with <u>wide</u> trac adapter.</p> |





# TRAC-MASTER®

Mounting Accessories

## MONOPOINTS and SPECIAL MOUNTINGS


### Low Voltage Monopoint Adapters

Example: T58 BL

| T58   | T539   |
|---|--|
| BL, BZ, SL, WH  | WH   |
| <p><b>Monopoint Adapter</b></p> <p>For T537, T538 or Trac-Lites R Series Low-Voltage Power Packs. Mounts directly to outlet box. Adapter is offset to accept all Power Pack styles. Power Pack latch locks in detent.</p>  | <p><b>Monopoint Low Voltage Cover</b></p> <p>Contains integral electronic transformer. Designed to accept one Juno 12V halogen low voltage trac spotlight directly to Juno's 6" recessed universal housings.</p>  |


### Low Voltage Recessed Monopoint Adapters

Example: T543 WH

| T543  |
|---|
| WH  |
| <p><b>Monopoint Power Pack</b></p> <p>Monopoint Power Pack (recessed) for new construction. TC housing. Includes 50VA-12V magnetic transformer, pre-wired recessed housing, canopy, adjustable bar hangers and thermal protector. Designed to accept one Juno 12V halogen low voltage trac spotlight.</p>  |

### Low Voltage Coil – Cord Clamp-Ons

Example: T135 WH

| T135   |
|--|
| BL, WH   |
| <p><b>12V Low Voltage Monopoint</b></p> <p>12V Low Voltage Monopoint attaches to <b>T537</b> or <b>T538</b>. 2' Coil Cord extends to 5'. Accepts one Juno 12V low voltage spotlight.</p>  |