


**TRAC-MASTER®**

Mounting Accessories

# **MONOPOINTS and SPECIAL MOUNTINGS**

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_





Contact/Phone: \_\_\_\_\_




## **PRODUCT DESCRIPTION**

Special adapters permit the flexibility of mounting trac lights in various ways to meet special requirements.

## **Line Voltage Monopoint Adapters**


Example: T40N BL

<b>T40N</b>	<b>T40F</b>	<b>T41N</b>	<b>T42N</b>
<b>BL, SL, WH</b>	<b>BL, SL, WH</b>	<b>BL, SL, WH</b>	<b>BL, WH</b>
<b>Monopoint Adapter</b> Mounts directly to outlet box. Accepts one 120V Juno trac fixture. 	<b>Flush Monopoint Adapter</b> Mounts directly to 4" outlet box only. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter. 	<b>Duo-Point Adapter</b> Mounts directly to an outlet box. Accepts two 120V Juno trac fixtures. 	<b>Weighted Base</b> For portable use. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture. 

<b>T45</b>	<b>T46</b>	<b>T57N</b>
<b>BL, WH</b>		<b>WH</b>
<b>Pin-Up/Monopoint Adapter</b> Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter. 	<b>Clamp/Monopoint Adapter</b> Clamps to pipe or planking up to 2-1/2" thick. Accepts one 120V Juno trac fixture. Supplied with 8' three-wire cord and plug. 	<b>Monopoint Line Voltage Cover</b> Attaches one 120V trac fixture directly to Juno's 6" recessed universal housings. 

## **Line Voltage Coil – Cord Clamp-Ons**

Example: T132 WH

<b>T132</b>	<b>T132 WA</b>	<b>T133</b>	<b>T133 WA</b>
<b>BL, WH</b>	<b>BL, WH</b>	<b>BL, WH</b>	<b>BL, WH</b>
<b>120V Monopoint with Trac Adapter</b> 120V Monopoint with trac adapter for electrical connection to Trac. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.	<b>120V Monopoint with Trac Adapter</b> Same as <b>T132</b> but accepts one 120V Juno Trac fixture with wide trac adapter.	<b>120V Monopoint with Male Plug</b> 120V Monopoint with male plug (120V) attaches to receptacle. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.	<b>120V Monopoint with Male Plug</b> Same as <b>T133</b> but accepts one 120V Juno Trac fixture with wide trac adapter.
2' Coil Cord extends to 5'. 1-3/4" Clamp opening. 			


**TRAC-MASTER®**

Mounting Accessories

**MONOPOINTS  
and SPECIAL MOUNTINGS****Line Voltage Extension Wands**


Examples: TEW 12IN BL, TEWS WH WA

TEW	TEW WA	TEWS	TEWS WA
12IN, 18IN, 24IN, 36IN, 48IN	12IN, 18IN, 24IN, 36IN, 48IN		
BL, SL, WH	BL, SL, WH	BL, SL, WH	BL, SL, WH
<b>Line Voltage Extension Wands</b>  For use with one or two circuit trac and line voltage monopoints. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.	<b>Line Voltage Extension Wands</b>  Same as <b>TEW</b> but accepts one 120V Juno trac fixture with <u>wide</u> trac adapter.	<b>24" Wand Slope Adapter</b>  Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.	<b>24" Wand Slope Adapter</b>  Same as <b>TEWS</b> but accepts one 120V Juno trac fixture with <u>wide</u> trac adapter.

**Line Voltage Slope Ceiling Adapter**

Examples: T95 BL, T95 WH WA

T95	T95 WA
BL, BZ, SL, WH	BL, BZ, SL, WH
<b>Slope Ceiling Adapter</b>  Attaches to trac, permitting Trac-Master or Trac-Lites Trac fixtures with <u>standard size</u> trac adapter to be hung vertically from sloped ceiling. 90° maximum adjustable	<b>Slope Ceiling Adapter</b>  Same as above but accepts one 120V Juno Trac fixture with <u>wide</u> trac adapter.





**TRAC-MASTER®**


Mounting Accessories

**MONOPOINTS  
and SPECIAL MOUNTINGS****Low Voltage Monopoint Adapters**

Example: T58 BL

<b>T58</b>	<b>T539</b>
<b>BL, BZ, SL, WH</b>	<b>WH</b>
<p><b>Monopoint Adapter</b></p> <p>For T537, T538 or Trac-Lites R Series Low-Voltage Power Packs. Mounts directly to outlet box. Adapter is offset to accept all Power Pack styles. Power Pack latch locks in detent.</p> 	<p><b>Monopoint Low Voltage Cover</b></p> <p>Contains integral electronic transformer. Designed to accept one Juno 12V halogen low voltage trac spotlight directly to Juno's 6" recessed universal housings.</p> 

**Low Voltage Recessed Monopoint Adapters** Example: T543 WH

<b>T543</b>
<b>WH</b>
<p><b>Monopoint Power Pack</b></p> <p>Monopoint Power Pack (recessed) for new construction. TC housing. Includes 50VA-12V magnetic transformer, pre-wired recessed housing, canopy, adjustable bar hangers and thermal protector. Designed to accept one Juno 12V halogen low voltage trac spotlight.</p> 

**Low Voltage Coil – Cord Clamp-Ons** Example: T135 WH

<b>T135</b>
<b>BL, WH</b>
<p><b>12V Low Voltage Monopoint</b></p> <p>12V Low Voltage Monopoint attaches to <b>T537</b> or <b>T538</b>. 2' Coil Cord extends to 5'. Accepts one Juno 12V low voltage spotlight.</p> 