


RLL1 Specification Sheet

Project Name:	Location:	MFG: Philips Hadco
Fixture Type:	Catalog No.:	Qty:



Ordering Guide

Example: RLL1 A

Product Code	RLL1
Finish	A Black

Specifications

- HOUSING:**
Die-cast aluminum faceplate with galvanized steel, single gang recessed box with stainless steel fasteners. Gasketing is diecut neoprene.
- FINISH:**
Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.
- OPTICAL ASSEMBLY:**
Frosted tempered glass lens.
- LAMPING:**
12W maximum S-8 (93) lamp. Lamp is included with fixture.
- ELECTRICAL ASSEMBLY:**
Single contact bayonet (S-8). 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.
- WARRANTY:**
Three-year limited warranty.
- CERTIFICATIONS:**
Manufactured to ISO 9001:2008 Standards.
- Height :**
2 13/16" (71mm)
- Width:**
4 5/8" (116mm)
- Depth:**
2 3/4" (70mm)
- Max. Weight:**
1.2 lb