



LytePro 7 LED Wall Sconce

LPW7-8DGY

LPW7, 14W COB LED, 350mA, 4000K, 120-277V, Dark gray textured paint – 82 lm/W

The low profile silhouette and compact appearance of LytePro 7 LED wall sconces have high appeal across many building styles. Its low profile styling is ideally suited for use over doorways, garages, entranceways, wall signs or any applications where a lower mounting height and compact size is desired. LytePro 7 utilizes only 14 watts, and achieves up to 86 LPW to provide an efficient alternative to traditional light sources.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000k
CRI	70
Photometric Distribution Type	Type II
Mounting	Wall
B.U.G. Rating	B1U0G1
Operating and Electrical	
Voltages	120/208/240/277 V
Luminaire Input Watts	14
Approval and Application	
Safety Listing	ETL

Initial Performance (IEC Compliant)	
Luminaire Lumens	1200
Efficacy	82 lm/W
Application Conditions	
Max Ambient Temp	+40 °C
Min Ambient Temp	-30 °C
Product Data	
Order product name	LPW7-8DGY
EAN/UPC - Product	190096011193
Order code	912400531018
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400531018

LytePro 7 LED Wall Sconce

Net Weight (Piece)	0.001 kg
Catalog Number	LPW7-8DGY
Catalog Number Description	LPW7, 14W COB LED, 350mA, 4000K, 120-277V, Dark gray textured paint

