

# Closed-End Splice Connectors and Terminals

CONSTRUCTION PRODUCTS  
**BUCHANAN**

## Splice Caps/Termend® Lugs

Buchanan Construction Products offers a comprehensive, time-proven splicing system for splicing, insulating and terminating.

- Just two sizes needed to splice solid or stranded wires ranging from 2 #18 AWG through 3 #8 AWG or 2 #6 AWG. Snap-on nylon insulators, rated at 105°C, provide a convenient, safe and fast way to insulate the splice.
- "One-size-fits-all" copper Termend® lugs, available in ring, spade, and locking spade types for various stud sizes. Terminate wires from #16 through #8.

### Splice Cap Crimp Connectors

Color	Packaging			Cat. No.
	Type	Unit	Std.	
Copper	Box	100	1,000	2006S
Steel No Twist		100	1,000	2008S
Copper		50	500	2011S
Copper	Bag	1,000	10,000	2006SB
Steel No Twist		1,000	10,000	2008SB
Copper		500	5,000	2011SB

### Splice Cap Insulators

Type	Packaging			Cat. No.
	Unit	Std.		
Box	100	1,000		2007
	50	500		2014
Bag	1,000	10,000		2007B
	500	5,000		2014B



### Termend® Lugs

Stud Size	Tongue Type	Packaging			Cat. No.
		Type	Unit	Std.	
6	Ring	Box	50	500	16-8-6
8			50	500	16-8-8
10			50	500	16-8-10
1/4			50	500	16-8-1/4
6	Spade	Box	50	500	16-8-6S
8			50	500	16-8-8S
10			50	500	16-8-10S
6	Locking Spade	Box	50	500	16-8-6L
8			50	500	16-8-8L
10			50	500	16-8-10L

### Crimp Tool

Type	Packaging			Cat. No.
	Unit	Std.		
Bag	1	1		C24

### Wire Combinations (Copper Wire Only)

Wire Combinations						Cat. No.
#18	#16	#14	#12	#10		
2 to 10 1 w/1 to 6#16 1 w/1 to 5#14 1 w/1 to 3#12 1 w/1#10 1 to 3 w/1 to 5#16 1 to 3 w/1 to 4#14 1 to 3 w/1 to 2#12 1 to 2 w/1#10	2 to 7 1 w/1 to 8#18 1 w/1 to 4#14 1 w/1 to 3#12 or 1#10 1 to 3 w/1 to 5#18 2 w/1 to 2#12 or 1#10 3 w/1 to 2#14 or 1#12 3 w/1#10	2 to 5 1 w/1 to 7#18 1 w/1 to 4#16 1 w/1 to 3#12 or 1#10 1 to 3 w/1 to 4#18 1 w/1 to 2#16 3 w/1#12	2 to 4 1 w/1 to 6#18 1 w/1 to 4#16 1 w/1 to 3#14 or 1#10 1 or 2 w/1 to 4#18 1 or 2 w/1 to 2#16 1 w/1#10	2 1 w/1 to 5#18 1 w/1 to 3#16 1 w/1 to 2#14 or 1#12 2 w/1 #18 and 1#16		2006S 2008S
#14	#12	#10	#8	#6	#4	2011S
5 to 11 Stranded 4 to 10 Solid 1 to 3 w/3 to 5#12 1 to 3 w/1 to 4#10 5 to 8 w/1 to 3#12	3 to 7 Stranded 3 to 6 Solid 1 to 3 w/5 to 8#14 3 to 5 w/1 to 3#14 1 or 2 w/3 to 4#10	2 to 5 Stranded 2 to 4 Solid 3 or 4 w/1 to 3#14 3 or 4 w/1 to 2#12 1 w/1#8 1 w/1#6 or 1#4	2 or 3 Stranded 2 Solid 1 w/1#10 1 w/1#6 or 1#4 1 w/2 or 4#14	2 Stranded 1 Stranded w/1#8 1 Stranded w/1#10	1 Stranded w/1#8 1 Stranded w/1#10	
#18	#16	#14	#12	#10		2002
2 to 6 Stranded 3 to 5 Solid	2 to 3 Stranded 2 to 3 Solid	2 Stranded 2 Solid	1 w/1#14 Stranded 1 w/2#18 Solid	1 Stranded		
Termend® Lugs						
1#16 through 1#18 Stranded (or equivalent combination of 2 or more wires)						
1#16 through 1#10 Solid (or equivalent combination of 2 or more wires)						