


3-Phase/Motor Rotation Testers

Features



- Identifies three-phase sequence
 - Indicates motor rotation
 - Checks for open phases
 - For use up to 600V
 - 2-year warranty
- Includes carrying case



61-521
3-Phase Sequence
and Rotation Tester



Features



- For use up to 600V
 - Color-coded insulators over alligator clips
 - Shock resistant housing
 - Easy to read
 - 2-year warranty
- Includes carrying case



61-520
3-Phase
Sequence



Digital Light Meter

Features

- Wide lighting range
 - Foot candle and lux measurement
 - Remote light sensor
 - Cosine and color corrected
 - Peak hold
 - Low battery indication
 - 2-year warranty
- Includes carrying case



61-681
Digital Light Meter



Specifications	61-681	
	RANGE & RESOLUTION	ACCURACY
FOOT CANDLES	20.00/200.00/2000.0/200000	2%
LUX	20.00/200.00/2000.0/200000	2%

Infrared Thermometer

Features

- Measurement range: -76°F to 932°F
- Distance spot: 12:1
- Modes: Ave., Difference, Hi/Low limits w/alarm, Max, Min, Lock
- Emissivity Range: Adjustable from 0.1 to 1
- Precision K-type thermocouple (optional)
- Backlight
- Auto power off
- Low battery indicator
- 2-year warranty



61-685
Infrared Thermometer



Accessories

Optional	
K-type Thermocouple	61-461

Specifications	61-685	
	RANGE & RESOLUTION	ACCURACY
TEMPERATURE OF OBJECT	-27 to 932°F (-33 to 500°C)	+/- 4°F (+/-2°C) of reading or whichever is greater
AMBIENT TEMPERATURE	73 +/-5°F (23 +/-3 °C)	