





Economy Fans


A quality fan for an incredible value

- Permanently lubricated motor, requires no maintenance
- cUL and UL listed for use over bathtubs and showers (when connected to a GFCI protected branch circuit)

 • Housing Dimension: 7-1/2" x 7-1/4" x 3-5/8"
- Low-profile, washable, white plastic grille: 9-1/4" x 9-3/4"
- Rugged steel housing with double strength steel mounting flanges with key hole slots for fast installation
- 3" round duct connector
- Compact housing fits between joists or studs allowing for ceiling or wall installation
 Fits 2"x 4" constructions
- Dynamically balanced impeller blower
- Torsion spring grille mounting means no tools are required to install grille
- Available in single and project packs for builder convenience

SPECIFICATIONS

MODEL	CFM AT 0.1" SP*	L/s** AT 0.1" SP	SONES AT 0.1" SP	POWER RATING	AMPS	SHIPPING WEIGHT (POUNDS)	PROJECT PACK (QTY. 6)	HOUSING PACK (QTY. 6)
E050	50	23.6	2.5	120/60	1.1	3.5	E0F50	1667H
E070	70	33.0	4.0	120/60	1.5	3.7	E0F70	1667H









^{*} Static pressure ** Litres per second