


# MODELS DX50L & DX70L DELUXE COMBINATION VENTILATION FAN/LIGHT



Quiet, high performance fan / light with a modern styled, low profile grille.

### FEATURES

#### GRILLE:

- Low profile styling
- Up to 100W incandescent lamp capacity (bulb not included)
- White polymeric grille with shatter resistant light diffusing lens

#### BLOWER:

- Plug-in permanently lubricated motor, requires no maintenance
- Centrifugal blower wheels for high capacity and low sound levels
- Low RPM for quiet performance
- Dynamically balanced centrifugal blower wheel yields a high efficient performance

#### HOUSING:

- Mounts between joists or directly to framing members
- Tapered 4" (101.6 mm) round, polymeric duct connector - prevents metallic clatter
- Built-in mounting ears for a quick and secure installation
- Rugged galvanized steel construction

NOTE: Product is designed for installation in ceilings up to a 12/12 pitch

### TYPICAL SPECIFICATION

Ventilator shall be Broan Model DX50L or DX70L.

Ventilator shall have a galvanized steel housing. It shall be ducted to a roof or wall cap using 4" (101.6 mm) round ductwork. Automatic back draft damper shall be located within duct connector.


Blower assembly shall have a centrifugal-type blower wheel and have a permanently-lubricated motor. Blower shall also operate at a low RPM rating. Bulb shall be rated at a maximum of 100W and be of an incandescent type.

Air delivery shall be no less and sound levels no greater than listed. All air and sound ratings shall be certified by HVI. Units shall be cUL listed. Units shall be cUL listed for use in insulated ceilings (Type I.C.) with up to an R40 rating.


### SPECIFICATIONS

MODEL	VOLTS	AMPS*	Hz	SONES	CFM (L/s)	ROUND DUCT (mm)
DX50L	120	1.1	60	2.5	50 (23.6)	4" (101.6 mm)
DX70L	120	2.0	60	3.5	70 (33.0)	4" (101.6 mm)

\*Total Connected Load



HVI-2100 CERTIFIED RATINGS comply with new testing technologies and procedures prescribed by the Home Ventilating Institute, for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. (2.54 mm) static pressure, based on tests conducted in AMCA's state-of-the-art test laboratory. Sones are a measure of humanly-perceived loudness, based on laboratory measurements.



Broan-NuTone Canada Inc., 1140 Tristar Drive, Mississauga, Ontario, Canada L5T 1H9 (1-888-882-7626)

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by <span style="float: right;">Date</span>