

FEATURES & SPECIFICATIONS

INTENDED USE — Our recessed LED module is the most economical means to create a well lit environment with exceptional energy efficiency and near zero maintenance. Great for retrofit into existing downlight cans or new construction and remodel applications. Compliant friction clip retention allows fitment into nearly 100% of installed cans. The LED module maintains at least 70% light output for 35,000 hours. Indoor and Outdoor Use.

CONSTRUCTION — Aluminum spun reflector with deep regression for reduced glare. Combined LED and driver printed circuit board attached. Inner reflector cone funnels light through the pressed-in diffused lens.

OPTICS — Diffused lens at end of mixing chamber to provide even light distribution for general illumination, equivalent to 65W BR30 Lamp.

Wide flood beam angle at > 45°.

ELECTRICAL — Center 2 Edge™ (patent pending) technology created for a single point source. Primary power disconnect provided for simple connection to a dedicated LED connector in the housing.

Dimming down to 10%. For compatible dimmers, refer to [Compatible Dimmers Chart](#).

700-lumen E series has an input wattage of 10 watts, 70 lumens per watt, equivalent to 65-watt incandescent.

E Series' patent pending driver has zero inrush which allows power loads to be calculated with actual rated wattages.

Example: 60 units of 4BEMW LED fixtures can be installed in line with a 600-watt dimmer. 600W/10W = 60 fixtures.

INSTALLATION — Suitable for installation in standard height rough-in sections.

E26 socket adaptor and ships standard, except for the 27K version in the state of California.

Friction clips allow fitment into cans with an inside diameter of 4.0" to 4.5".

LISTINGS — CSA certified to US and Canadian safety standards. ENERGY STAR® certified. Can be used to comply with California Title 24 Part 6 High Efficacy LED Light Source Requirements. Wet location listed. WSEC ASTM E283 for Air-Tight (with IC housings).

WARRANTY — 5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

PATENTS PENDING.

Catalog Number
Notes
Type

LED Recessed Downlighting

4BE/4SE



E26 adaptor

Specifications


Aperture: 4-1/8 (10.5)

Ceiling opening: Determined by rough-in

Overlap trim: 5-1/4 (13.3)

Height: 2-1/2 (6.3)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

All configurations of this product are considered "standard" and have short lead times.

Example: 4BEMW LED 27K 90CRI L3LED T24

Series/Finish	Lamp	CCT / W / Lumens ¹	CRI	Voltage	Options	Housing Options
4BEMW 4" Baffle LED module, matte white	LED	27K 2700K / 9.8W / 650L ² 30K 3000K / 9.8W / 700L	90CRI 90CRI	(blank) 120V	L/SKTWHIP No E26 Adapter (CA only)	L3LED T24 4" new construction rough-in LED base L3RLED T24 4" remodel rough-in LED base
4SEMW 4" Smooth LED module, matte white		35K 3500K / 10W / 700L 40K 4000K / 9.8W / 720L 50K 5000K / 9.8W / 700L				L3 4" new construction rough-in ³ L3R 4" remodel rough-in ³ IC1 4" new construction housing ³

Accessories: Order as separate catalog number.		
<table> <tr> <td>RK1 CG52178 E26 ADAPTER/MALE PLUG BAL DISC ASM</td> <td>E26 Adapter</td> </tr> </table>	RK1 CG52178 E26 ADAPTER/MALE PLUG BAL DISC ASM	E26 Adapter
RK1 CG52178 E26 ADAPTER/MALE PLUG BAL DISC ASM	E26 Adapter	

Notes

- Total system delivered lumens.
- L/SKTWHIP must be selected for 27K product shipping to California.
- Must be ordered on a separate line.

4" LED Module

PHOTOMETRICS

Distribution Curve	Distribution Data	Output Data	Coefficient of Utilization	Illuminance Data at 30" Above Floor for a Single Luminaire
--------------------	-------------------	-------------	----------------------------	--

4BEMW LED, 27K, input watts: 9.8, delivered lumens: 656, LM/W = 66, test no. ISF 35431, tested in accordance with IESNA LM 79-08

Distribution Curve	Ave Lumens			Zone Lumens % Lamp			pf pc pw	80%			20%			50%			50% beam - 59.8°	10% beam - 100.2°
	Ave	Lumens		Zone	Lumens	% Lamp		50%	30%	10%	50%	30%	10%	50%	30%	10%		
	0	330		0° - 30°	246.3	37.6		0	119	119	119	116	116	116	111	111		
	5	329	31	0° - 40°	385.5	58.8	1	107	103	100	105	101	99	100	98	95	Inital FC Mounting Center Height Beam Diameter FC Diameter FC 8.0 10.9 6.3 5.5 13.1 1.1 10.0 5.9 8.6 2.9 17.9 0.6 12.0 3.7 10.9 1.8 22.7 0.4 14.0 2.5 13.2 1.2 27.5 0.2 16.0 1.8 15.5 0.9 32.3 0.2	
	15	312	88	0° - 60°	591.1	90.1	2	95	90	85	94	88	84	90	86	82		
	25	278	127	0° - 90°	655.8	100.0	3	86	79	73	84	78	72	81	76	71		
	35	224	139	90° - 120°	0.0	0.0	4	77	69	63	76	69	63	73	67	62		
	45	158	122	90° - 130°	0.0	0.0	5	70	62	56	69	61	56	67	60	55		
	55	94	84	90° - 150°	0.0	0.0	6	64	55	50	63	55	49	61	54	49		
	65	41	42	90° - 180°	0.0	0.0	7	58	50	45	57	50	44	56	49	44		
	75	16	18	0° - 180°	655.8	*100.0	8	53	46	40	53	45	40	51	45	40		
	85	5	5	*Efficiency			9	49	42	37	49	41	37	48	41	36		
	90	0					10	46	38	33	45	38	33	44	38	33		

4BEMW LED, 30K, input watts: 9.8, delivered lumens: 706, LM/W = 71, test no. ISF 35431P1, tested in accordance with IESNA LM 79-08

Distribution Curve	Ave Lumens			Zone Lumens % Lamp			pf pc pw	80%			20%			50%			50% beam - 59.8°	10% beam - 100.2°
	Ave	Lumens		Zone	Lumens	% Lamp		50%	30%	10%	50%	30%	10%	50%	30%	10%		
	0	355		0° - 30°	265.3	37.6		0	119	119	119	116	116	116	111	111		
	5	355	34	0° - 40°	415.1	58.8	1	107	103	100	105	101	99	100	98	95	Inital FC Mounting Center Height Beam Diameter FC Diameter FC 8.0 11.7 6.3 5.9 13.1 1.2 10.0 6.3 8.6 3.2 17.9 0.6 12.0 3.9 10.9 2.0 22.7 0.4 14.0 2.7 13.2 1.3 27.5 0.3 16.0 1.9 15.5 1.0 32.3 0.2	
	15	336	95	0° - 60°	636.5	90.1	2	95	90	85	94	88	84	90	86	82		
	25	299	137	0° - 90°	706.3	100.0	3	86	79	73	84	78	72	81	76	71		
	35	241	150	90° - 120°	0.0	0.0	4	77	69	63	76	69	63	73	67	62		
	45	170	131	90° - 130°	0.0	0.0	5	70	62	56	69	61	56	67	60	55		
	55	101	90	90° - 150°	0.0	0.0	6	64	55	50	63	55	49	61	54	49		
	65	44	45	90° - 180°	0.0	0.0	7	58	50	45	57	50	44	56	49	44		
	75	17	19	0° - 180°	706.3	*100.0	8	53	46	40	53	45	40	51	45	40		
	85	5	6	*Efficiency			9	49	42	37	49	41	37	48	41	36		
	90	0					10	46	38	33	45	38	33	44	38	33		

4BEMW LED, 35K, input watts: 9.8, delivered lumens: 706, LM/W = 70, test no. ISF 35431P2, tested in accordance with IESNA LM 79-08

Distribution Curve	Ave Lumens			Zone Lumens % Lamp			pf pc pw	80%			20%			50%			50% beam - 59.8°	10% beam - 100.2°
	Ave	Lumens		Zone	Lumens	% Lamp		50%	30%	10%	50%	30%	10%	50%	30%	10%		
	0	355		0° - 30°	265.3	37.6		0	119	119	119	116	116	116	111	111		
	5	355	34	0° - 40°	415.1	58.8	1	107	103	100	105	101	99	100	98	95	Inital FC Mounting Center Height Beam Diameter FC Diameter FC 8.0 11.7 6.3 5.9 13.1 1.2 10.0 6.3 8.6 3.2 17.9 0.6 12.0 3.9 10.9 2.0 22.7 0.4 14.0 2.7 13.2 1.3 27.5 0.3 16.0 1.9 15.5 1.0 32.3 0.2	
	15	336	95	0° - 60°	636.5	90.1	2	95	90	85	94	88	84	90	86	82		
	25	299	137	0° - 90°	706.3	100.0	3	86	79	73	84	78	72	81	76	71		
	35	241	150	90° - 120°	0.0	0.0	4	77	69	63	76	69	63	73	67	62		
	45	170	131	90° - 130°	0.0	0.0	5	70	62	56	69	61	56	67	60	55		
	55	101	90	90° - 150°	0.0	0.0	6	64	55	50	63	55	49	61	54	49		
	65	44	45	90° - 180°	0.0	0.0	7	58	50	45	57	50	44	56	49	44		
	75	17	19	0° - 180°	706.3	*100.0	8	53	46	40	53	45	40	51	45	40		
	85	5	6	*Efficiency			9	49	42	37	49	41	37	48	41	36		
	90	0					10	46	38	33	45	38	33	44	38	33		

4BEMW LED, 40K, input watts: 9.8, delivered lumens: 727, LM/W = 73, test no. ISF 35431P3, tested in accordance with IESNA LM 79-08


Distribution Curve	Ave Lumens			Zone Lumens % Lamp			pf pc pw	80%			20%			50%			50% beam - 59.8°	10% beam - 100.2°
	Ave	Lumens		Zone	Lumens	% Lamp		50%	30%	10%	50%	30%	10%	50%	30%	10%		
	0	366		0° - 30°	272.8	37.6		0	119	119	119	116	116	116	111	111		
	5	365	35	0° - 40°	427.0	58.8	1	107	103	100	105	101	99	100	98	95	Inital FC Mounting Center Height Beam Diameter FC Diameter FC 8.0 12.1 6.3 6.0 13.1 1.2 10.0 6.5 8.6 3.3 17.9 0.6 12.0 4.1 10.9 2.0 22.7 0.4 14.0 2.8 13.2 1.4 27.5 0.3 16.0 2.0 15.5 1.0 32.3 0.2	
	15	346	97	0° - 60°	654.7	90.1	2	95	90	85	94	88	84	90	86	82		
	25	308	141	0° - 90°	726.5	100.0	3	86	79	73	84	78	72	81	76	71		
	35	248	154	90° - 120°	0.0	0.0	4	77	69	63	76	69	63	73	67	62		
	45	175	135	90° - 130°	0.0	0.0	5	70	62	56	69	61	56	67	60	55		
	55	104	93	90° - 150°	0.0	0.0	6	64	55	50	63	55	49	61	54	49		
	65	46	46	90° - 180°	0.0	0.0	7	58	50	45	57	50	44	56	49	44		
	75	18	20	0° - 180°	726.5	*100.0	8	53	46	40	53	45	40	51	45	40		
	85	5	6	*Efficiency			9	49	42	37	49	41	37	48	41	36		
	90	0					10	46	38	33	45	38	33	44	38	33		

4" LED Module

PHOTOMETRICS

Distribution Curve	Distribution Data	Output Data	Coefficient of Utilization	Illuminance Data at 30" Above Floor for a Single Luminaire
--------------------	-------------------	-------------	----------------------------	--

4BEMW LED, 50K, input watts: 9.8, delivered lumens: 706, LM/W = 71, test no. ISF 35431P4, tested in accordance with IESNA LM 79-08



ADDITIONAL DATA 4BEMW/4SEMW LED 27K

4" ENERGY DATA	
Lumens	650
Color Temperature	2700K
CRI	90
Lu/Watts	65
Operating temp	-20°C (-4°F) to 40°C (104°F)
EMI/RFI	FCC Title 47 CFR, Part 15, Class B
Sound rating	Class A Standards
Input voltage	120V
Min. power factor	0.99
Input frequency	50/60 Hz
Rated wattage	9.8W
Input power	9.8W
Input current	0.08A

ADDITIONAL DATA 4BEMW/4SEMW LED 30K

4" ENERGY DATA	
Lumens	700
Color Temperature	3000K
CRI	90
Lu/Watts	70
Operating temp	-20°C (-4°F) to 40°C (104°F)
EMI/RFI	FCC Title 47 CFR, Part 15, Class B
Sound rating	Class A Standards
Input voltage	120V
Min. power factor	0.99
Input frequency	50/60 Hz
Rated wattage	9.8W
Input power	9.8W
Input current	0.08A

ADDITIONAL DATA 4BEMW/4SEMW LED 35K

4" ENERGY DATA	
Lumens	700
Color Temperature	3500K
CRI	90
Lu/Watts	70
Operating temp	-20°C (-4°F) to 40°C (104°F)
EMI/RFI	FCC Title 47 CFR, Part 15, Class B
Sound rating	Class A Standards
Input voltage	120V
Min. power factor	0.99
Input frequency	50/60 Hz
Rated wattage	10W
Input power	10W
Input current	0.08A

ADDITIONAL DATA 4BEMW/4SEMW LED 40K

4" ENERGY DATA	
Lumens	720
Color Temperature	4000K
CRI	90
Lu/Watts	70
Operating temp	-20°C (-4°F) to 40°C (104°F)
EMI/RFI	FCC Title 47 CFR, Part 15, Class B
Sound rating	Class A Standards
Input voltage	120V
Min. power factor	0.99
Input frequency	50/60 Hz
Rated wattage	9.8W
Input power	9.8W
Input current	0.08A

ADDITIONAL DATA 4BEMW/4SEMW LED 50K

4" ENERGY DATA	
Lumens	700
Color Temperature	5000K
CRI	90
Lu/Watts	70
Operating temp	-20°C (-4°F) to 40°C (104°F)
EMI/RFI	FCC Title 47 CFR, Part 15, Class B
Sound rating	Class A Standards
Input voltage	120V
Min. power factor	0.99
Input frequency	50/60 Hz
Rated wattage	9.8W
Input power	9.8W
Input current	0.08A