


VENTILATOR FAN/LIGHT COMBINATION MODEL 763RLN & 769RL



Efficient ventilation and bright light in one easy installation.

FEATURES

LIGHT FIXTURE

- Fan and light operates separately or together
- Uses one (1) 100 watt bulb (bulb not included)


BLOWER

- Quiet operation with one-piece molded blower wheel, silent backdraft damper - no metallic clatter
- One-piece polypropylene wheel 4-3/4" (121 mm) in diameter
- Plug-in motor and light
- Shaded pole, thermally protected motor
- For baths up to 45 sq. ft. (4.18 m²), other rooms up to 60 sq. ft. (5.57 m²)

HOUSING

- Rugged galvanized steel construction 9" x 9" x 5-3/4" (229 mm x 229 mm x 146 mm)
- Non-yellowing, white polymeric grille with break resistant lens 12-1/4" x 10-3/4" (311 mm x 273 mm)
- 4" (102 mm) duct fitting with built-in silent backdraft damper
- Mounting flange provided

NOTE: Not for use in kitchens. Not for use with solid state speed controls.



HVI-2100 CERTIFIED RATINGS comply with new testing technologies and procedures prescribed by the Home Ventilating Institute, for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. (2.54 mm) static pressure, based on tests conducted in AMCA's state-of-the-art test laboratory. Sones are a measure of humanly-perceived loudness, based on laboratory measurements.

TYPICAL SPECIFICATIONS

Combination unit shall be NuTone model 763RLN or 769RL.


Combination unit shall have galvanized steel housing 9" x 9" x 5-3/4" (229 mm x 229 mm x 146 mm), and be connected to a white polymeric grille 12-1/4" x 10-3/4" (311 mm x 273 mm). It shall be ducted to ceiling using 4" (102 mm) round ductwork. Silent backdraft damper shall be located within duct connector. Listed for use in insulated ceilings (Type I.C.).

Combination unit shall have plug-in motor and light. Motor shall be thermally protected. Blower wheel shall be composed of one-piece polypropylene, and be 4-3/4" (121 mm) in diameter.

Air delivery to be no less than 50 CFM (23.6 L/s) model 763RLN, 70 CFM (33 L/s) model 769RL, and sound level to be no greater than 2.5 Sones model 763RLN, 3.0 Sones model 769RL. Suitable for use over tub or shower enclosure when insulated in a GFCI protected branch circuit. Air and sound ratings shall be certified by the HVI. Unit shall be cUL and UL listed.

SPECIFICATIONS

MODEL	VOLTS	AMPS	SONES	CFM (L/s)	DUCT (mm) Rd.
763RLN	120	1.4	2.5	50 (23.6)	4" (102)
769RL	120	2.0	3.0	70 (33)	4" (102)



NuTone Inc., 4820 Red Bank Road, Cincinnati, OH 45227 (1-800-543-8687)
Broan-NuTone Canada Inc., 1140 Tristar Drive, Mississauga, Ontario, Canada L5T 1H9 (1-888-882-7626)

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date