BRSAN®

Central Vacuums Selection Guide BREAN BROAN BROAN BROAN

Broan vacuums: A successful blend of innovation and efficiency

Broan has always been innovating and creating central vacuums that make the competition green with envy. We aim to offer you efficient, high-performance vacuums that exceed your expectations with respect to housekeeping and simplify the cleaning of your home.

Made in Canada and designed to the highest standards of quality, some of our products allow you to clean up to 12,000 sq. ft. of surface area, all while maintaining superior suction.

Our engineers are constantly working to innovate and develop new technologies in order to reduce the noise level of our appliances. All Broan power units are equipped with a sound suppression system that requires absolutely no need for an external muffler - an innovative feature meant to increase your comfort.

Offered in two Series, Broan central vacuum systems are sold separately or as kits that include: The power unit, hose, tools and brushes. You are sure to find a model that suits your needs.

By browsing this buying guide, you will be able to select the Broan central vacuum system that best suits your needs.

- 1. EVALUATE THE SQUARE FOOTAGE of your home.

 (include all rooms to clean with the central vacuum)

 _______ sq. ft.
- 2. Based on the square footage, SELECT THE APPROPRIATE POWER of Broan central vacuum system.
 Up to 3,000 sq. ft.: Pages 4 to 7
 Up to 6,000 sq. ft.: Page 8
- 3. Depending on the MAIN FLOORING TYPE in the house, choose the appropriate Broan central vacuum kit. Look for the



4. Estimate the number of required wall inlets: House square footage sq. ft.

Up to 12,000 sq. ft.: Page 9

illustrations below to quide you.

÷ 600 = _____, rounded up to _____ wall inlets.

Ex.: 2,800 sq. ft. ÷ 600 = 4.6







CXKIT350A Kit

The ideal compact solution for limited spaces.

THE KIT INCLUDES:

- 120 volts CX350 power unit with disposable bag
- Standard accessory kit BN135
- Multi-surface brush BN160
- 30' standard crushproof hose BN30LV

CXKIT450A Kit

The best value for hard flooring.

THE KIT INCLUDES:

- 120 volts CX450 power unit (also available separately)* with disposable bag (permanent filter in option)
- Standard accessory kit BN135
- Multi-surface brush BN160
- 30' standard crushproof hose BN30LV







Hard floor





CXKIT450E Kit

An hybrid model for all types of flooring.

THE KIT INCLUDES:

- 120 volts CX450 power unit (also available separately)*
 with disposable bag (permanent filter in option)
- Deluxe accessory kit BN235
- Electric power brush BN200
- 32' dual-voltage crushproof hose BN32DV

VXKIT300A Kit

Quiet, efficient and ideal for hard flooring.

THE KIT INCLUDES:

- 120 volts VX3000C power unit (also available separately)* with permanent filter
- Standard accessory kit BN135
- Air-driven brush BN165
- 32' low-voltage crushproof hose BN32LV



VXKIT600E Kit

Efficiency combined with high-quality HEPA filtration.

THE KIT INCLUDES:

- 120 volts VX6000C power unit (also available separately)* with high-quality HEPA permanent filter
- Deluxe accessory kit BN235
- Electric power brush BN200
- 32' dual-voltage crushproof hose BN32DV

VXKIT1200E Kit

The ultimate power for all flooring types and home sizes.

THE KIT INCLUDES:

- 240 volts VX12000C power unit (also available separately)*
 with high-quality HEPA permanent filter
- Deluxe accessory kit BN235
- Electric power brush BN200
- 32' dual-voltage crushproof hose BN32DV

Technical Specifications





СХ







٧x

1 year

1 year



KIT	CXKIT350A	CXKIT450A	CXKIT450E	VXKIT300A	VXKIT600E	VXKIT1200E
Power unit	CX350	CX450	CX450	VX3000C	VX6000C	VX12000C
Power unit available separately		•	•	•	•	•
Max. square footage of the home	2,800	3,000	3,000	3,000	6,000	12,000
Power (air-watt)	400	450	450	475	550	1040
Flooring type	Hard floor	Hard floor	Hard floor & carpet	Hard floor	Hard floor & carpet	Hard floor & carpet
Total recommended number of wall inlets	5	5	5	5	10	20
Air flow (CFM)	100	100	100	114	135	230
Disposable bag	•	•	•			
Permanent filter		Optional	Optional	•	•	•
HEPA filter					•	•
Debris pail capacity (L)	22.7	22.7	22.7	15	26.5	26.5
Control	Rocker switch	Rocker switch	Rocker switch	Electronic 1 LED	Electronic 5 LEDs	Electronic 5 LEDs
Dimensions CX: (Ø x H) VX: (D x W x H) (in.)	11 x 24	11 x 40.5	11 x 40.5	11.5 x 16.5 x 36	11.5 x 17.5 x 39	11.5 x 17.5 x 39
Voltage	120	120	120	120	120	240
Current rating (Amp)	8.5	8.5	8.5	12	12.5	13.5
Recommended circuit (Amp)	15	15	15	15	15	20
Motor(s) warranty	3 years	3 years	3 years	5 years	5 years	5 years

INCLUDED ACCESSORIES IN THE KIT

1 year

Accessories warranty

10

BN160 - Multi-Surface brush	•	•				
BN165 - Air-driven brush				•		
BN200 - Electric power brush			•		•	•
BN135 - 6-piece standard accessory kit	•	•		•		
BN235 - 7-piece deluxe accessory kit			•		•	•
BN30LV - 30' standard crushproof hose	•	•				
BN32LV - 32' low-voltage crushproof hose				•		
BN32DV - 32' dual-voltage crushproof hose			•		•	•

1 year

1 year

1 year

11

INSTALLATION ACCESSORIES

Broan offers a wide range of practical installation accessories that will harmonize to your interior design.




VacuSweep™ Inlet Valve

- Makes it easy for debris and dirt to be swept and removed from non-carpet surfaces
- Available in white (V600W), ivory (V600) and black (V600B)



VacuSweep™ Trim Plate

- Available in white (V601W), ivory (V601) and black (V601B)



BRSAN

A successful blend of innovation and efficiency

Broan-NuTone Canada 1140, Tristar Drive Mississauga (Ontario) L5T 1H9 CANADA

Customer Service: 1-888-882-7626 (905) 670-2500

www.broan.ca



87590 02/12