


DOUBLE/SINGLE POLE THERMOSTATS MODELS 1T22, 1T22W & 1D23W



Designed with the installer in mind, attractive thermostats available in beige or white to fit any modern decor.

FEATURES

- Thermostats available in two colours - beige and white
- Thermostat unit to be installed 4 ft. - 5 ft. (1.2 m - 1.5 m) above floor
- Controls temperature ranges from 10°C to 30°C
- To be utilised for electrical baseboard heating systems
- Utilises quadrex mounting screws
- Bi-metallic sensing strips facilitate thermostat installation
- Install unit away from concealed pipes, ducts and open draft ways
- Units equipped with an electrical insulation (FISH PAPER) for added fire protection
- FISH PAPER specifications are as follows:
 1. Thickness: 0.031 mm
 2. Highest possible dielectric strength for a fiber
 3. Arcs when exposed to an electrical circuit overload
 4. 10.3 kV/mm - Perpendicular Dielectric Strength at a 0.254 mm thickness
 5. 1.25 MPa Bursting Strength at 0.254 mm thickness

SPECIFICATIONS

MODEL	MAXIMUM AMPS	VOLTAGE	TYPE	COLOUR
1T22	22 A	120/240 VAC	SINGLE POLE	BEIGE
1T22W	22 A	120/240 VAC	SINGLE POLE	WHITE
1D23W	22 A	120/240 VAC	DOUBLE POLE	WHITE


TYPICAL SPECIFICATION

Thermostat shall be Broan Model 1T22, (1T22W) or (1D23W). Thermostat shall be constructed with a non warping metal base.


Connection wire ends come factory stripped to ensure a proper connection is made. All wiring and connections must conform to local applicable codes and ordinances.

Units are to be CSA certified.

WIRING DIAGRAMS



DOUBLE POLE THERMOSTAT



SINGLE POLE THERMOSTAT



BROAN-NU-TONE CANADA INC., MISSISSAUGA, ONTARIO WWW.BROAN.CA 1-888-882-7626

PROJECT	REMARKS
LOCATION	
MODEL No.	
QTY.	
SUBMITTED BY	
DATE	