


MODEL XB90C VENTILATION FAN



FEATURES

UltraGreen™ Energy Saving DC Motor

- DC motor for efficiency well beyond ENERGY STAR® requirements.
- LEED and Energy Star for Homes compliant.

UltraSilent™ Sound Technology

- HVI certified, best-achievable <0.3 Sone level provides nearly silent operation for a relaxing environment.
- State-of-the-art blower and duct outlet design smooths airflow.
- High tech DC motor designed for nearly silent operation.

UltraSmart™ Control Technology

 Powerful operation maintained over a wide range of real-world installations (CFM ratings maintained through at least 0.25" static pressure).


UltraQuick™ Installation Technology

- Unique telescoping mounting frame fits through retrofit drywall opening to allow easy installation from the room side. No attic access needed!
- · Captive screws allow for easy new construction installation.
- Mounting frame positioning tabs provide easy vertical positioning for new construction.
- Easy to insert and remove snap-in housing. No screws required!
- · Easy to insert and remove snap-in blower.
- Inside or outside duct connector and knockout plate mounting provides flexibility for new construction or retrofit.

cUL Listed for use over bathtubs and showers when connected to a GFCI protected branch circuit (ceiling mount only).

3-year warranty.

DIMENSIONS



NOTE: Dimensions shown are in inches.





Broan-NuTone Canada; Mississauga, Ontario www.broan.ca 877-896-1119

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date



PERFORMANCE SPECIFICATIONS MODEL XB90C VENTILATION FAN

Efficacy (CFM/Watt)

13.6

0.25 Ps

Airflow (CFM)

90

ELECTRICAL & WEIGHT

Volts	Hz	Amps	Shipping Weight (lb.)
120	60	0.1	12.5





Airflow (CFM)

90

HVI PERFORMANCE

Sound (Sones)

< 0.3

6" Duct

Power

(Watts)

6.6

0.1 Ps - Static Pressure (in. H2O)

HVI-2100 CERTIFIED RATINGS comply with new testing technologies and procedures prescribed by the Home Ventilating Institute, for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. static pressure, based on tests conducted in a state-of-the-art test laboratory. Sones are a measure of humanly-perceived loudness, based on laboratory measurements.

Airflow (CFM)

90

4" Duct

Power

(Watts)

9.5

Efficacy (CFM/Watt)

9.4

0.25 Ps

Airflow (CFM)

89

0.1 Ps - Static Pressure (in. H₂O)

Sound (Sones)

0.5



FAN CAPABILITY

