



Economy Fans

A quality fan for an incredible value



- Permanently lubricated motor requires no maintenance
- UL listed for use over bathtubs and showers when connected to a GFCI protected branch circuit
- Housing Dimensions: 8-1/16" x 7-3/8" x 3-7/8"
- Fits 2" x 4", 2" x 6", 2" x 8" constructions
- Low-profile, washable white polymeric grille: 9-5/8" x 8-5/8"
- Torsion spring grille mounting means no tools are required to install grille
- Rugged steel housing with double strength mounting flanges with key hole slots for fast installation
- 3" round duct connector
- Compact size facilitates installation between framing members
- Dynamically balanced impellor based blower
- Available in single and project packs for builder convenience

SPECIFICATIONS

| MODEL | CFM AT 0.1" SP* | L/s** AT 0.1" SP | SONES AT 0.1" SP | POWER RATING | AMPS | SHIPPING WEIGHT (POUNDS) | PROJECT PACK (QTY. 6) | HOUSING PACK (QTY. 6) |
|-------|-----------------|------------------|------------------|--------------|------|--------------------------|-----------------------|-----------------------|
| 696NC | 50 | 23.6 | 3.0 | 120/60 | 1.1 | 3.6 | 696NCB | 690AC |
| 695C | 70 | 33.0 | 4.5 | 120/60 | 1.5 | 4.1 | 695CB | 690AC |

* Static pressure.

** Litres per second.



Dimensions shown are in inches.



87531B