

CENTRAL VACUUM KIT MODEL CXKIT450E



CX450 POWER UNIT SPECIFICATIONS

Motor	1-Stage
Horsepower Rating	1.74 @ Full Open Intake
Ampere	8.5
Voltage	120 VAC
Airflow at 2" (50.8 mm) opening	.100 CFM (47.2 L/s)
Water Lift	.90" (2.3 m)
Air Watts	.450
Switch on Power Unit	Yes
Recommended Circuit	15 Amp
Primary Filtration	Disposable Bag
Capacity	6 U.S. Gallons (22.7 Litres)
Secondary Filtration	Yes
cULus Listed	Yes
Housing	Black metal housing with polymeric debris pail
Power Unit Dimensions	∅ 11" x 40½" H

Designed for smaller homes up to 3,000 square feet (278 m²), this power unit features a 1-stage motor that delivers 450 air watts of power. A great solution for the budget minded consumer.

FEATURES

- Integrated muffler for quiet operation
- Wall-mount bracket for simple, safe, and secure mounting
- Left and right intake ports for easy installation
- Oversized debris pail handles made for a quick and easy pail removal
- Large 6 U.S. gallons (22.7 litres) easy-clean, corrosion resistant debris pail that typically needs emptying only every 6 months

- Disposable bag for easy maintenance
- Optional permanent filter (provides the option of changing from a disposable bag to a permanent filter) (part no. PF450)
- Six foot (1.8 m) long power cord
- Deluxe accessory kit including:
 - Deluxe electric power brush with aluminum telescopic wand, 32' dual-voltage crushproof hose, deluxe hose hanger, 12" wide hard floor brush, stainless steel ratchet telescopic wand, natural bristle upholstery tool, deluxe square faced dusting brush, 12" crevice tool with notched end, clip-on caddy, caddy bag
- cULus Listed
- Limited Lifetime Warranty



Broan-NuTone Canada Inc.; Mississauga, Ontario www.broan.ca 1-888-882-7626

PROJECT	REMARKS
LOCATION	
MODEL NO.	
QTY.	
SUBMITTED BY	
DATE	