# SPECIFICATION SHEET

# BRSAN

# MODEL SPK110 SPEAKER FAN

### DESCRIPTION

#### BLOWER:

- Plug-in, permanently lubricated motor engineered for continuous operation
- Dynamically balanced centrifugal blower wheel for quiet, efficient performance
- Low RPM for quiet operation

#### HOUSING:

- Rugged, 26 gauge, galvanized steel construction
- Polymeric, 4" round duct connector with tapered sleeve and no metallic clatter
- 7-5/8" height allows for 2" x 8" ceiling installations
- Sturdy, easy, four-point mounting directly to joist
- Includes unique spacer (patent pending) for mounting to engineered "I" joists
- Can be mounted in ceilings up to 12/12 pitch

#### GRILLE:

- Polymeric construction
- Innovative design the result of extensive research with designers and consumers

#### SPEAKER ASSEMBLY:


- Dual High-Fidelity Sensonic<sup>™</sup> speakers with *Bluetooth*<sup>®</sup> wireless technology
- Brilliant audio performance concealed behind the fan grille
- Play any audio through most *Bluetooth*<sup>®</sup> wireless technology enabled devices

#### CONTROLS (Purchase separately):

- Refer to Broan's catalog for a complete line of accessories to effectively adapt these fans to your construction requirements.
- U.L. Listed for use over bathtubs and showers when connected to a GFCI protected branch circuit (ceiling mount only).

Broan-NuTone LLC Hartford, Wisconsin

3-Year Warranty



### **TYPICAL SPECIFICATION**

Fan shall be Broan Model SPK110.

Fan shall have corrosion resistant galvanized steel housing with four-point mounting capability. It shall be ducted to a roof or wall cap using 4" round ductwork.

Blower assembly shall be removable, have a centrifugaltype blower wheel and a permanently lubricated motor designed for continuous operation.

Speaker assembly shall be removable and play audio files when paired with most *Bluetooth*<sup>®</sup> wireless technology enabled devices.

Non-metallic damper/duct connector shall be included.

Air delivery shall be no less than 110 CFM and sound level no greater than 1.0 Sone. All air and sound ratings shall be certified by HVI.

Fan shall be ENERGY STAR<sup>®</sup> qualified and have an energy efficient permanent split capacitor motor.

Fan shall be U.L. Listed for use over bathtubs and showers when connected to a GFCI protected branch circuit.



# **Bluetooth**°

www.broan.com 800-558-1711

The *Bluetooth*<sup>®</sup> word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Broan-NuTone LLC is under license. Other trademarks and trade names are those of their respective owners.

Broan-NuTone Canada ULC Mississauga, Ontario www.broan.ca 888-882-7626						
REFERENCE	QTY.	REMARKS	Project			
			Location			
			Architect			
			Engineer			
			Contractor			
			Submitted by Date			

# **PERFORMANCE RATINGS MODEL SPK110 SPEAKER FAN**

### **HVI PERFORMANCE**

Model	Static Pressure (Ps)	CFM	Sones	Fan Watts	
SPK110	0.10	110	1.0	43.6	
SPKIIU	0.25	101			





HVI-2100 CERTIFIED RATINGS comply with new testing technologies and procedures prescribed by the Home Ventilating Institute, for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. static pressure, based on tests conducted in a state-of-the-art test laboratory. Sones are a measure of humanly-perceived loudness, based on laboratory measurements.

AMPS			WEIGHT ——		
Model	Amps		Model	Shipping	

SPK110	0.9		Weight
		SPK110	11.0 lbs.








NOTE: Dimensions shown are in inches.



## AIR FLOW PERFORMANCE -



Broan-NuTone LLC Hartford, Wisconsin www.broan.com 800-558-1711 Broan-NuTone Canada ULC Mississauga, Ontario www.broan.ca 888-882-7626