

SYNTHETIC SERIES
18 GAUGE CUT RESISTANT

99-1-9772

HPPE 18 Gauge Cut Resistant Synthetics

Available Sizes:

7-11 (S-X2L)

Shell:

HPPE (High Performance Polyethylene) 18 Gauge seamless knit shell

Coating:

Nitrile foam (palm and fingers)

Wrist:

Elastic knit wrist

Cuff:

Colour coded bound hem

Lining:

Unlined

Labelling:

BDG logo, part number and CE Ratings printed back hand

Packaging:

12 pr per Polybag 120 pr per Carton

Features & Benefits:

- High Performance Polyethylene fiber shell provides cut resistance, dexterity and comfort
- Nitrile foam coating for an excellent wet/dry and light oil grip
- Seamless knit construction provides excellent dexterity and comfort
- CE/EN388:
Abrasion Resistance Level 4
Cut Resistance Level 5
Tear Resistance Level 4
Puncture Resistance Level 4
- ANSI Cut Level 4 (1925 Grams)

Applications:

- Automotive • Metal Fabrication • Shipping/Receiving • Construction
- Handling Sharp/Abrasive Objects • Injection Molding

**18
GAUGE**



CE	CUT LEVEL	
EN388	EN388	ANSI
4544	5	4
		1925 g



Cut Resistant



Abrasion Resistance



Breathable



Dexterity



Grip

HPPE (High Performance Polyethylene)
18 Gauge fiber for the ultimate heavy duty
protection in an ultra light weight glove