

slide-to-off dimmers



- slide up to brighten, down to dim
- small control shown
- large control measures 4.56" x 4.56" (fits into a 1-gang backbox)

incandescent/halogen (small control)

single pole	600 W	N-600-
single pole	1000 W	N-1000-

incandescent/halogen (large control)

single pole	1500 W	N-1500-
single pole	2000 W	N-2000-

magnetic low-voltage* (small control)

single pole	600 VA (450 W)	NLV-600-
-------------	-------------------	-----------------

magnetic low-voltage* (large control)

single pole	1000 VA (800 W)	NLV-1000-
single pole	1500 VA (1200 W)	NLV-1500-

Suggested maximum lighting load for magnetic low-voltage dimming is 450 W for 600 VA products, 800 W for 1000 VA products, and 1200 W for 1500 VA products to allow for transformer losses.

electronic low-voltage* (small control)

single pole	450 W	NELV-450-
-------------	-------	------------------

neon/cold cathode* (small control)

single pole	600 VA	NLV-600-
-------------	--------	-----------------

neon/cold cathode* (large control)

single pole	1000 VA	NLV-1000-
single pole	1500 VA	NLV-1500-

* requires neutral wire connection

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and Hi-lume® LED



- slide up to brighten, down to dim
- small control shown
- large control measures 4.56" x 4.56" (fits into a 1-gang backbox)
- no derating if ganged

fluorescent* (small control)

single pole	120V 16A	NF-10-
-------------	----------	---------------

fluorescent (large control)

single pole	277V 8A	NF-10-277-
-------------	---------	-------------------

LED with Hi-lume® LED driver only*

NEW

single pole	120V 16A	NF-10-
-------------	----------	---------------

LED (large control)

single pole	277V 8A	NF-10-277-
-------------	---------	-------------------

fluorescent dimming (preset dimmers)



- slider button turns lights on/off
- slide up to brighten, down to dim
- no derating if ganged

fluorescent* (small control)

single pole/3-way	120V 8A	NF-103P-
single pole/3-way	277V 6A	NF-103P-277-

LED with Hi-lume® LED driver only*

NEW

single pole/3-way	120V 8A	NF-103P-
single pole/3-way	277V 6A	NF-103P-277-

* requires neutral wire connection



Shown actual size: Nova® dimmer in white (WH) (includes wallplate)

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- electronic low-voltage lighting
- neon/cold cathode
- fluorescent lighting
- LED lighting
- fully variable fan controls

control locations

- single pole (one location)
- 3-way (two locations)

available colors (see page 14 for color swatches)

colors (matte finish)

WH white	GR gray
BE beige	TP taupe
IV ivory	BR brown
AL almond	BL black
LA light almond	SI sienna

CAD file downloads available at www.lutron.com/cad

Multi-gang, screwless, seamless wallplates available – wallplate selector tool at www.lutron.com/lutron/wallplate

NOVA® original slide dimmers

product family features

- visible heat sink (see page 46)
- slide adjusts light to suit any activity
- full family of controls plus matching fan controls, switches and wiring devices
- dimmer includes 1-gang wallplate
- use “no fins broken” wallplates for full wattage capacity in multi-gang applications
- does not mount with Nova T[☆]® under common wallplate
- voltage compensation maintains stable light levels despite line voltage variations

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com