

preset dimmers



- tapswitch turns on/off
- slide up to brighten, down to dim
- includes hidden locator light in white, beige, ivory, and taupe models only

incandescent/halogen, magnetic low-voltage

single pole dimming/ multi-location switching	600W/VA	V-600-	
single pole dimming/ multi-location switching	1000W/VA	V-1000-	

For multi-location switching with Vareo® auxiliary electronic tapswitches, VETS-R-. Not for use with mechanical 3-way or 4-way switches. Suggested maximum lighting load for magnetic low-voltage dimming is 450W for 600VA products and 800W for 1000VA products, to allow for transformer losses.

electronic low-voltage

use **VF-10-** plus **ELVI-1000** for loads up to 1000W of electronic transformer low-voltage sources @ 120V (page 171).

use **V-600-** plus **PHPM-PA-DV + LUT-LBX** for loads up to 16A of electronic transformer low-voltage sources @ 277V (page 169).

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and Hi-lume® LED



- use with Lutron® 3-wire line-voltage control electronic dimming ballasts
- please refer to the Lutron® Fluorescent Dimming Systems Selection Guide (P/N 366-002) for more information
- must be derated if ganged

fluorescent*

single pole dimming/ multi-location switching	20 ballasts 8A	VF-10-	
--	-------------------	---------------	--

LED with Hi-lume® LED driver only* NEW

single pole dimming/ multi-location switching	20 drivers 8A	VF-10-	
--	------------------	---------------	--

LED with GRX-TVI (0-10 VDC sink control)* NEW

single pole dimming/ multi-location switching	16A load 30 mA control 120/277V	VF-10-	
---	---------------------------------------	---------------	--

For multi-location switching, use Vareo® auxiliary electronic tapswitches, VETS-R-. Not for use with mechanical 3-way or 4-way switches.

* requires neutral wire connection

See page 19 for available colors.

To order, add color suffix to model number.
Example: **V-600- WH**



Shown actual size: Vareo® dimmer in white (WH) (includes wallplate)

VAREO® tapswitch™ dimmers

product family features

- exclusive dimmer/switch size opening
- tapswitch returns light to your favorite level
- slide adjusts light to suit any activity
- sophisticated thin-profile
- dimmer includes 1-gang wallplate
- use “no fins broken” wallplates for full wattage capacity in multi-gang applications
- voltage compensation maintains stable light levels despite line voltage variations

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- fluorescent lighting
- LED lighting

control locations

- single pole (one location)
- multi-location switching

available colors

(see page 14 for color swatches)

colors (matte finish)

- | | |
|------------------------|------------------|
| WH white | GR gray |
| BE beige | TP taupe |
| IV ivory | BR brown |
| AL almond | BL black |
| LA light almond | SI sienna |

metals (special finishes)

- | | |
|--------------------------|-------------------------|
| SB satin brass | SC satin chrome |
| BB bright brass | SN satin nickel |
| BC bright chrome | BN bright nickel |
| QB antique brass | AU gold plated |
| QZ antique bronze | |

anodized aluminum

- | | |
|------------------|------------------|
| CLA clear | BRA brass |
| BLA black | |

Custom colors and finishes are available by providing Lutron® with a paint color number, swatch, or sample. Lutron® can color match your controls. Contact Customer Service at 1.888.LUTRON1.

Multi-gang, screwless, seamless wallplates available – wallplate selector tool at www.lutron.com/lutron/wallplate

CAD file downloads available at www.lutron.com/cad

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com