



# Hospital Grade Straight Blade Receptacles

2 Pole, 3 Wire Grounding  
15A 125V, 20A 125V  
15A 250V, 20A 250V


## Duplex and Single Receptacles

### FEATURES


- Exclusive 5-leaf nickel-plated brass line contacts ensure lowest heat rise, smooth plug blade insertion, long-term retention and corrosion resistance.
- Rigid, glass reinforced nylon base lends ultimate strength and superior high heat resistance in contact carrier.
- Unique screw terminal guards provide fast, easy insulation from conductive surfaces.
- 0.050" (1.27mm) solid brass, nickel-plated mounting strap with non-riveted, integral one-piece grounding system for highest durability – assures superior ground integrity and corrosion resistance under heaviest use.
- High impact and chemical-resistant nylon face.
- Tapered lead-in slots on back wiring holes assist in gathering stranded wires for faster, more secure connections.
- All terminal (H-N-G) and mounting screws nickel-plated, triple combination (slot/Phillips/Robertson) head for superior corrosion resistance and maximum flexibility.
- Long, broad mounting strap helps reach large panel cutouts for Code Compliance.
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper used.
- Screw-Catch™ feature on duplex devices speeds mounting of wallplates.
- Long-life neon bulb in illuminated devices easily identifies emergency circuits.

INDUSTRIAL  
COMMERCIAL  
RESIDENTIAL


## A-1 STRAIGHT BLADE RECEPTACLES



**8200**



**8300**



**8310**

### Back and Side Wire

Rating A	V/AC	NEMA	Color	Catalog No.		
				Duplex	Duplex Illuminated	Single†
15	125	5-15R	Black	8200BK	—	—
			Brown	8200B	—	8210B
			Gray	8200GY	—	8210GY
			Red	8200RD	8200LTRD	8210RD
			Ivory	8200V	8200LTV	8210V
			White	8200W	8200LTW	8210W
20	125	5-20R	Black	8300BK	—	—
			Brown	8300B	—	8310B
			Gray	8300GY	—	8310GY
			Red	8300RD	8300LTRD	8310RD
			Ivory	8300V	8300LTV	8310V
			White	8300W	8300LTW	8310W
15	250	6-15R	Ivory	8600V*	—	8610V*
			White	8600W*	—	8610W*
20	250	6-20R	Brown	8400B*	—	8410B*
			Gray	8400GY*	—	8410GY*
			Red	8400RD*	—	8410RD*
			Ivory	8400V*	—	8410V*
			White	8400W*	—	8410W*

\*Not NOM certified

†Single receptacles meet all UL, CSA & Federal Specifications, but differ in design and construction from duplexes noted above.

### TESTING & CODE COMPLIANCE

- Meets all UL 498 Hospital Grade requirements, Federal Spec. WC-596
- UL Listed, (file no. E15058).
- CSA Certified, (file no. 6914 (6233-01)), Meets all CSA requirements, C22.2 no. 42.
- NOM Certified, except as noted.

### MATERIAL CHARACTERISTICS

Meets flammability requirements per UL 94, V2 rated. Temperature Rating: Duplex receptacles: -20° C to 70 °C; Single receptacles: -20°C to 60°C.



**5-15R**



**5-20R**



**6-15R**



**6-20R**